



Product data sheet

Power tools for trade & industry

HGS 88/150

INDUSTRIAL HGS 88/150



The machine must not be operated without the protective guard

The most important data

Permitted sanding disc diameter	150 mm
No-load speed	5,700 rpm
Rated power, output	2,200 W

Part Number 0 602 240 134

Technical data

Technical data

Frequency	300 Hz
Voltage	200 V
Permitted sanding disc diameter	150 mm
No-load speed	5,700 rpm
Rated power, input	2,900 W
Rated power, output	2,200 W
Rated current	10 A
Weight as per EPTA	8.4 kg
Toolholder, drive end	M14
Switch version	Safety switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

