

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



QUICKON panel feed-through, for external panel mounting with manual solder/slip-on connection, 2.8 x 0.8 mm. 4-pos.

Commercial data

Item number	1640650
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF6
Product key	AF6HAA
Catalog page	Page 16 (PC-2002)
GTIN	4017918188733
Weight per piece (including packing)	21.51 g
Weight per piece (excluding packing)	20.45 g
Customs tariff number	85369010
Country of origin	PL

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

Technical data

Product properties

Product type	Panel feed-through
Number of positions	4
Position marking	1, 2, 3, 4
Number of connections	4
Number of connections per position	1
Shielded	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection method On the device side	Manual solder/slip on connection
Frequency of connections between conductors of the same cross section	10 (if the conductor is connected more than once, seal and cap may need to be replaced.)

Conductor connection

Conductor cross section flexibel	0.34 mm ² ... 0.75 mm ²
Conductor cross section solid	0.34 mm ² ... 0.75 mm ²
Connection cross section AWG	18 ... 16
Tightening torque Union nut	2.5 Nm
Tightening torque Contact carrier	3.75 Nm
Tightening torque Locking nut	3.75 Nm
Wrench size Union nut	22 mm
Wrench size Contact carrier	22 mm

Dimensions

Dimensional drawing	
Width	22 mm
Height	22 mm
Length	42.3 mm

Electrical properties

Rated surge voltage (III/3)	4 kV
Contact resistance	< 3 mΩ
rated voltage (II/2)	320 V (with insulating sleeve)

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

rated voltage (III/2)	160 V (with insulating sleeve)
Rated voltage (III/3)	160 V (with insulating sleeve)
Nominal voltage U_N	160 V AC
	160 V DC
Nominal current I_N	9 A

Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Material Contact	Cu alloy
Material Contact surface	Sn
Flammability rating according to UL 94	V0
Material wire insulation	PVC / PE

Cable/line

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	Class 2-6 // 0.34 mm ² : 0.1 mm; 0.5 - 0.75 mm ² : 0.15 mm
Wire diameter including insulation	2.5 mm
Position marking	1, 2, 3, 4

Mounting

Mounting type	Front mounting M20
Assembly note	If the conductor is reconnected, it must be cut off above the last contact point. QUICKON components may only be operated when under no load.

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Impact strength	IK06
Ambient temperature (operation)	-25 °C ... 80 °C (Specifications of the cable manufacturer must be observed.)
	-25 °C ... 50 °C (when the conductor is connected. Specifications of the cable manufacturer must also be observed.)
Temperature when conductor connected	-5 °C ... 50 °C

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through




1640650

<https://www.phoenixcontact.com/in/products/1640650>

Drawings

Dimensional drawing



Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1640650>

	cUL Recognized Approval ID: E118976			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	6 A	-	-

	UL Recognized Approval ID: E118976			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	9 A	-	-

	EAC Approval ID: RU C-DE.A*30.B.01102			

cULus Recognized				
-------------------------	--	--	--	--

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

Classifications

ECLASS

ECLASS-11.0	27440602
ECLASS-12.0	27440602
ECLASS-13.0	27440602

ETIM

ETIM 9.0	EC002566
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

Accessories

Q-MU M20 - Nut

1640702

<https://www.phoenixcontact.com/in/products/1640702>

Nut (plastic) to lock the contact carrier from the inside of the device



Q-PROT 9/11 - Filler plug

1670235

<https://www.phoenixcontact.com/in/products/1670235>

Closing cap for Pg9/Pg11 to close unoccupied connections



Q 0,75/4FL/11-M20KU-ESA - Panel feed-through



1640650

<https://www.phoenixcontact.com/in/products/1640650>

PT/FS 2,8 - Insulating sleeve

1406700

<https://www.phoenixcontact.com/in/products/1406700>

Insulating sleeve, as touch protection, slide onto the conductor before for 2.8 slip-on sleeves



MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/in/products/1212489>



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in