

**Enclosure
KLIPPON K01****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon® has stood for competence and quality in enclosures. The enclosures are ideal for turnkey customised solutions for standard industrial applications and for explosive-risk applications.

Improved products that meet all application requirements: this was Weidmüller's aim during the update of the Klippon® K housing series. Weidmüller delivers many types of aluminium enclosures; they are designed to fit precisely with a wide range of customer requirements and applications.

Our comprehensive product line provides the following advantages:

- Available in two different surfaces: natural and powder-coated (RAL 7001)
- Available normally with silicone or chloroprene gasket seal
- A uniform Torx-slotted screw head is used for over 19 different housing sizes.
- Mounting holes not within the sealed area
- High degree of protection: IP66, IP67 and IP68
- Impact resistance of up to 10 Joules
- The housings are certified by ATEX, GOST, GOST Ex, cULus, Russian Maritime Register, German Lloyd, as well as the empty housing standard.
- Alloy is resistant to salt water
- Standardised distributor housings with threaded holes and a variety of terminal configurations

General ordering data

Order No.	1565240000
Type	KLIPPON K01
Version	Enclosures, 64 mm, 34 mm, 58 mm, Aluminium AISi12
EAN	4008190134105
Qty.	10 pc(s).

Enclosure KLIPPON K01

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions

Length	34 mm	Width	58 mm
Height	64 mm	Mounting dimension - width	58 mm
Weight	120 g		

General information

Material	Aluminium AISi12	Mounting dimension - width	58 mm
Surface finish	untreated	Cover attachment	M4 torx stainless steel screws with slot
Enclosure attachment	Holes 4 mm	Impact resistance	10.00 J
Integral fixing	Threaded holes M3	Material	Aluminium AISi12
Seal material	Neoprene	Surface finish	untreated

Cable glands, left

M12 (3)	1	M16 (3)	1
---------	---	---------	---

Cable glands, right

M12 (2)	1	M16 (2)	1
Side of enclosure	left, right		

Cable glands, top/bottom

M12	1	M16	1
Side of enclosure	left, right		

horizontal assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5	1x1*	WDU 4 / ZDU 4	1x1*
-----------------------------	------	---------------	------

vertical assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	1x1*	WDU 4 / ZDU 4 (2)	1x1*
---------------------------------	------	-------------------	------

Classifications

ETIM 2.0	EC000058	ETIM 3.0	EC000058
ETIM 4.0	EC000058	UNSPSC	31-26-15-02
eClass 4.1	27-14-12-06	eClass 5.1	27-14-91-07
eClass 6.0	27-14-91-07		

Approvals

Approvals	CULUS; GERMLLOYD; GOSTME25; MARITREG; ROHS
-----------	--

Enclosure KLIPPON K01

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Drawings

