



SIMATIC S7-1200, CPU 1217C, CPU 1217C DC/DC/DC based on 6ES7217-1AG40-0XB0 with conformal coating -40...+60 °C . compact CPU, 2 PROFINET port onboard I/O: 10 DI 24 V DC; 4 DI RS-422/485; 6 DO 24 V DC; 0.5 A; 4 DO RS-422/485; 2 AI 0-10 V DC, 2 AO 0-20 mA power supply: DC 20.4-28.8V DC, program/data memory 150 KB 20.4-28.8V DC, program/data memory 150 KB



Figure similar

General information	
Product type designation	CPU 1217C DC/DC/DC
based on	<a href="#">6ES7217-1AG40-0XB0</a>
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	see entry ID: 109746275
Supply voltage	
Rated value (DC)	Yes
<ul style="list-style-type: none"> <li>24 V DC</li> </ul>	
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Load voltage L+	
<ul style="list-style-type: none"> <li>Rated value (DC)</li> <li>permissible range, lower limit (DC)</li> <li>permissible range, upper limit (DC)</li> </ul>	24 V 20.4 V 28.8 V
Input current	
Current consumption (rated value)	600 mA; CPU only
Current consumption, max.	1 600 mA; CPU with all expansion modules
Inrush current, max.	12 A; at 28.8 V DC
$I^2t$	0.5 A <sup>2</sup> ·s
Output current	
for backplane bus (5 V DC), max.	1 600 mA; Max. 5 V DC for SM and CM
Encoder supply	
24 V encoder supply	
<ul style="list-style-type: none"> <li>24 V</li> </ul>	L+ minus 4 V DC min.
Power loss	
Power loss, typ.	12 W
Memory	
Work memory	
<ul style="list-style-type: none"> <li>integrated</li> </ul>	150 kbyte
Load memory	
<ul style="list-style-type: none"> <li>integrated</li> <li>Plug-in (SIMATIC Memory Card), max.</li> </ul>	4 Mbyte with SIMATIC memory card
Backup	
<ul style="list-style-type: none"> <li>present</li> </ul>	Yes

<ul style="list-style-type: none"> <li>• maintenance-free</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• without battery</li> </ul>	Yes
<b>CPU processing times</b>	
for bit operations, typ.	0.08 µs; / instruction
for word operations, typ.	1.7 µs; / instruction
for floating point arithmetic, typ.	2.3 µs; / Operation
<b>CPU-blocks</b>	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
<b>OB</b>	
<ul style="list-style-type: none"> <li>• Number, max.</li> </ul>	Limited only by RAM for code
<b>Data areas and their retentivity</b>	
Retentive data area (incl. timers, counters, flags), max.	14 kbyte
<b>Flag</b>	
<ul style="list-style-type: none"> <li>• Size, max.</li> </ul>	8 kbyte; Size of bit memory address area
<b>Local data</b>	
<ul style="list-style-type: none"> <li>• per priority class, max.</li> </ul>	16 kbyte; Priority class 1 (program cycle): 16 KB, priority class 2 to 26: 6 KB
<b>Address area</b>	
<b>Process image</b>	
<ul style="list-style-type: none"> <li>• Inputs, adjustable</li> <li>• Outputs, adjustable</li> </ul>	1 kbyte 1 kbyte
<b>Hardware configuration</b>	
Number of modules per system, max.	3 comm. modules, 1 signal board, 8 signal modules
<ul style="list-style-type: none"> <li>• number of expansion boards (SB, CB, BB)</li> <li>• number of signal modules (SM)</li> <li>• number of communications modules (CM)</li> </ul>	1 8 3
<b>Time of day</b>	
<b>Clock</b>	
<ul style="list-style-type: none"> <li>• Hardware clock (real-time)</li> <li>• Backup time</li> <li>• Deviation per day, max.</li> </ul>	Yes 480 h; Typical ±60 s/month at 25 °C
<b>Digital inputs</b>	
Number of digital inputs	14; Integrated
<ul style="list-style-type: none"> <li>• of which inputs usable for technological functions</li> </ul>	6; HSC (High Speed Counting)
Sourcing/sinking input	Yes
<b>Number of simultaneously controllable inputs</b>	
all mounting positions	
— up to 40 °C, max.	14
<b>Input voltage</b>	
<ul style="list-style-type: none"> <li>• Rated value (DC)</li> <li>• for signal "0"</li> <li>• for signal "1"</li> </ul>	24 V 5 V DC at 1 mA 15 V DC at 2.5 mA
<b>Input delay (for rated value of input voltage)</b>	
for standard inputs	
— parameterizable	0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four
— at "0" to "1", min.	0.2 ms
— at "0" to "1", max.	12.8 ms
for interrupt inputs	
— parameterizable	Yes
for technological functions	
— parameterizable	Single phase: 3 @ 100 kHz & 3 @ 30 kHz, differential: 3 @ 80 kHz & 3 @ 30 kHz
<b>Cable length</b>	
<ul style="list-style-type: none"> <li>• shielded, max.</li> <li>• unshielded, max.</li> </ul>	500 m; 50 m for technological functions 300 m; for technological functions: No
<b>Digital outputs</b>	
Number of digital outputs	10
<ul style="list-style-type: none"> <li>• of which high-speed outputs</li> </ul>	4; 100 kHz Pulse Train Output

Limitation of inductive shutdown voltage to	L+ (-48 V)
Switching capacity of the outputs	
• with resistive load, max.	0.5 A
• on lamp load, max.	5 W
Output voltage	
• for signal "0", max.	0.1 V; with 10 kOhm load
• for signal "1", min.	20 V
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.1 mA
Output delay with resistive load	
• "0" to "1", max.	1 µs
• "1" to "0", max.	5 µs
Switching frequency	
• of the pulse outputs, with resistive load, max.	100 kHz
Relay outputs	
• Number of relay outputs	0
Cable length	
• shielded, max.	500 m
• unshielded, max.	150 m
<b>Analog inputs</b>	
Number of analog inputs	2
Input ranges	
• Voltage	Yes
Input ranges (rated values), voltages	
• 0 to +10 V	Yes
— Input resistance (0 to 10 V)	≥100k ohms
Cable length	
• shielded, max.	100 m; twisted and shielded
<b>Analog outputs</b>	
Number of analog outputs	2
Output ranges, current	
• 0 to 20 mA	Yes
<b>Analog value generation for the inputs</b>	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	10 bit
• Integration time, parameterizable	Yes
• Conversion time (per channel)	625 µs
<b>Analog value generation for the outputs</b>	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	10 bit
<b>Encoder</b>	
Connectable encoders	
• 2-wire sensor	Yes
<b>Interfaces</b>	
Number of PROFINET interfaces	1
<b>1. Interface</b>	
Interface type	PROFINET
Isolated	Yes
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Interface types	
• RJ 45 (Ethernet)	Yes
• Number of ports	2
• integrated switch	Yes
Protocols	
• PROFINET IO Controller	Yes

• PROFINET IO Device	Yes
• SIMATIC communication	Yes
• Open IE communication	Yes; Optionally also encrypted
• Web server	Yes
• Media redundancy	Yes
<b>PROFINET IO Controller</b>	
• Transmission rate, max.	100 Mbit/s
<b>Services</b>	
— PG/OP communication	Yes; encryption with TLS V1.3 pre-selected
— Isochronous mode	No
— IRT	No
— PROFinergy	No
— Prioritized startup	Yes
— Number of IO devices with prioritized startup, max.	16
— Number of connectable IO Devices, max.	16
— Number of connectable IO Devices for RT, max.	16
— of which in line, max.	16
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— Updating time	The minimum value of the update time also depends on the communication component set for PROFINET IO, on the number of IO devices and the quantity of configured user data.
<b>PROFINET IO Device</b>	
<b>Services</b>	
— PG/OP communication	Yes; encryption with TLS V1.3 pre-selected
— Isochronous mode	No
— IRT	No
— PROFinergy	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2
<b>Protocols</b>	
Supports protocol for PROFINET IO	Yes
PROFIsafe	No
PROFIBUS	Yes; CM 1243-5 (master) or CM 1242-5 (slave) required
OPC UA	Yes; OPC UA Server
AS-Interface	Yes; CM 1243-2 required
<b>Protocols (Ethernet)</b>	
• TCP/IP	Yes
• DHCP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
<b>Redundancy mode</b>	
<b>Media redundancy</b>	
— MRP	Yes; as MRP redundancy manager and/or MRP client
— MRPD	No
<b>SIMATIC communication</b>	
• S7 routing	Yes
<b>Open IE communication</b>	
• TCP/IP	Yes
— Data length, max.	8 kbyte
• ISO-on-TCP (RFC1006)	Yes
— Data length, max.	8 kbyte
• UDP	Yes
— Data length, max.	1 472 byte
<b>Web server</b>	
• supported	Yes
• User-defined websites	Yes
<b>OPC UA</b>	
• Runtime license required	Yes; "Basic" license required

<ul style="list-style-type: none"> <li>● OPC UA Server <ul style="list-style-type: none"> <li>— Application authentication</li> <li>— User authentication</li> <li>— Number of sessions, max.</li> <li>— Number of subscriptions per session, max.</li> <li>— Sampling interval, min.</li> <li>— Publishing interval, min.</li> <li>— Number of server methods, max.</li> <li>— Number of monitored items, recommended max.</li> <li>— Number of server interfaces, max.</li> <li>— Number of nodes for user-defined server interfaces, max.</li> </ul> </li> </ul>	<p>Yes; data access (read, write, subscribe), method call, runtime license required</p> <p>Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256</p> <p>"anonymous" or by user name &amp; password</p> <p>10</p> <p>5</p> <p>100 ms</p> <p>200 ms</p> <p>20</p> <p>1 000</p> <p>2</p> <p>2 000</p>
<b>Further protocols</b>	
<ul style="list-style-type: none"> <li>● MODBUS</li> </ul>	Yes
<b>Communication functions</b>	
<b>S7 communication</b>	
<ul style="list-style-type: none"> <li>● supported</li> <li>● as server</li> <li>● as client</li> <li>● User data per job, max.</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>See online help (S7 communication, user data size)</p>
<b>Number of connections</b>	
<ul style="list-style-type: none"> <li>● overall</li> </ul>	PG Connections: 4 reserved / 4 max; HMI Connections: 12 reserved / 18 max; S7 Connections: 8 reserved / 14 max; Open User Connections: 8 reserved / 14 max; Web Connections: 2 reserved / 30 max; OPC UA Connections: 0 reserved / 10 max; Total Connections: 34 reserved / 64 max
<b>Test commissioning functions</b>	
<b>Status/control</b>	
<ul style="list-style-type: none"> <li>● Status/control variable</li> <li>● Variables</li> </ul>	<p>Yes</p> <p>Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters</p>
<b>Forcing</b>	
<ul style="list-style-type: none"> <li>● Forcing</li> </ul>	Yes
<b>Diagnostic buffer</b>	
<ul style="list-style-type: none"> <li>● present</li> </ul>	Yes
<b>Traces</b>	
<ul style="list-style-type: none"> <li>● Number of configurable Traces</li> <li>● Memory size per trace, max.</li> </ul>	<p>2</p> <p>512 kbyte</p>
<b>Interrupts/diagnostics/status information</b>	
<b>Diagnostics indication LED</b>	
<ul style="list-style-type: none"> <li>● RUN/STOP LED</li> <li>● ERROR LED</li> <li>● MAINT LED</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>Integrated Functions</b>	
<b>Counter</b>	
<ul style="list-style-type: none"> <li>● Number of counters</li> <li>● Counting frequency, max.</li> </ul>	<p>6</p> <p>1 MHz</p>
<b>Frequency measurement</b>	
controlled positioning	Yes
Number of position-controlled positioning axes, max.	8
Number of positioning axes via pulse-direction interface	4; With integrated outputs
<b>PID controller</b>	
Number of alarm inputs	4
Number of pulse outputs	4
Limit frequency (pulse)	1 MHz
<b>Potential separation</b>	
<b>Potential separation digital inputs</b>	
<ul style="list-style-type: none"> <li>● Potential separation digital inputs</li> <li>● between the channels, in groups of</li> </ul>	<p>No</p> <p>1</p>
<b>Potential separation digital outputs</b>	
<ul style="list-style-type: none"> <li>● Potential separation digital outputs</li> </ul>	Yes

• between the channels	No
• between the channels, in groups of	1
<b>EMC</b>	
Interference immunity against discharge of static electricity	
• Interference immunity against discharge of static electricity acc. to IEC 61000-4-2	Yes
— Test voltage at air discharge	8 kV
— Test voltage at contact discharge	6 kV
Interference immunity to cable-borne interference	
• Interference immunity on supply lines acc. to IEC 61000-4-4	Yes
• Interference immunity on signal cables acc. to IEC 61000-4-4	Yes
Interference immunity against voltage surge	
• Interference immunity on supply lines acc. to IEC 61000-4-5	Yes
Interference immunity against conducted variable disturbance induced by high-frequency fields	
• Interference immunity against high-frequency radiation acc. to IEC 61000-4-6	Yes
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes; Group 1
• Limit class B, for use in residential areas	Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
<b>Degree and class of protection</b>	
IP degree of protection	IP20
<b>Standards, approvals, certificates</b>	
Siemens Eco Profile (SEP)	Siemens EcoTech
CE mark	Yes
Ecological footprint	
• environmental product declaration	Yes; type II acc. to ISO 14021
Global warming potential	
— global warming potential, (total) [CO2 eq]	143 kg
— global warming potential, (during production) [CO2 eq]	22 kg
— global warming potential, (during operation) [CO2 eq]	123 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-1.48 kg
<b>Ambient conditions</b>	
Free fall	
• Fall height, max.	0.3 m; five times, in product package
Ambient temperature during operation	
• min.	-40 °C; = Tmin; Startup @ -25 °C
• max.	60 °C; = Tmax; Tmax > 55 °C number of simultaneously switched-on digital inputs 5, current sinking/current sourcing (no adjacent points) and 4 differential inputs with horizontal mounting position; Tmax > 55 °C number of simultaneously switched-on digital inputs 3, current sinking (no adjacent points) and 4 differential outputs with horizontal mounting position
• vertical installation, min.	-40 °C; = Tmin; Startup @ -25 °C
• vertical installation, max.	50 °C; = Tmax
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	70 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
Relative humidity	
• With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation/frost (no commissioning under condensation conditions)
Vibrations	
• Vibration resistance during operation acc. to IEC 60068-2-6	2 g (m/s <sup>2</sup> ) wall mounting, 1 g (m/s <sup>2</sup> ) DIN rail

• Operation, tested according to IEC 60068-2-6	Yes
<b>Shock testing</b>	
• tested according to IEC 60068-2-27	Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
<b>Resistance</b>	
<b>Coolants and lubricants</b>	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
<b>Use in stationary industrial systems</b>	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75%) incl. salt spray according to EN 60068-2-52 (degree of severity 3). The supplied connector covers must remain on the unused interfaces during operation!
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust. The supplied connector covers must remain on the unused interfaces during operation!
<b>Use on ships/at sea</b>	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
— to chemically active substances according to EN 60721-3-6	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *
<b>Usage in industrial process technology</b>	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
<b>Remark</b>	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
<b>Pollutant concentrations</b>	
• SO2 at RH < 60% without condensation	SO2: < 0.5 ppm; H2S: < 0.1 ppm; RH < 60 % condensation-free
<b>Conformal coating</b>	
• Coatings for printed circuit board assemblies acc. to EN 61086	Yes; Class 2 for high reliability
• Protection against fouling acc. to EN 60664-3	Yes; Type 1 protection
• Military testing according to MIL-I-46058C, Amendment 7	Yes; Discoloration of coating possible during service life
• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal coating, Class A
<b>Configuration</b>	
<b>Programming</b>	
<b>Programming language</b>	
— LAD	Yes
— FBD	Yes
— SCL	Yes
<b>Know-how protection</b>	
• User program protection/password protection	Yes
• Copy protection	Yes
• Block protection	Yes
<b>Access protection</b>	
• protection of confidential configuration data	Yes
• Protection level: Write protection	Yes
• Protection level: Read/write protection	Yes
• Protection level: Complete protection	Yes
• User administration	Yes; device-wide
• Number of users	42
• Number of groups	14
• Number of roles	20
<b>Cycle time monitoring</b>	
• adjustable	Yes

Dimensions	
Width	150 mm
Height	100 mm
Depth	75 mm

Weights	
Weight, approx.	530 g

Classifications			
		Version	Classification
	eClass	14	27-24-22-07
	eClass	12	27-24-22-07
	eClass	9.1	27-24-22-07
	eClass	9	27-24-22-07
	eClass	8	27-24-22-07
	eClass	7.1	27-24-22-07
	eClass	6	27-24-22-07
	ETIM	10	EC000236
	ETIM	9	EC000236
	ETIM	8	EC000236
	ETIM	7	EC000236

Approvals / Certificates	
General Product Approval	Environment



[China RoHS](#)



last modified:

7/30/2025