

Eaton 088343

Catalog Number: 088343

Eaton Moeller® series RMQ16 Insert label, transparent, 2 82LQ18

General specifications



Product Name	Catalog Number
Eaton Moeller® series RMQ16	088343
Accessory Insert label	EAN
	4015080883432
Product Length/Depth	Product Height
1 mm	14 mm
Product Width	Product Weight
14 mm	0.7 g
Compliances	
CE	

Product specifications

Type

Transparent insert plates

Features

Labelled

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

Resources

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004136.pdf](#)

[DA-DC-00004158.pdf](#)

Drawings

[116C198](#)

eCAD model

[ETN.088343.edz](#)

Installation instructions

[IL04716016Z](#)

mCAD model

[lq18.stp](#)

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Connection to SmartWire-DT

No

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Built-in diameter

16 mm

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

0 A

Static heat dissipation, non-current-dependent P_{vs}

0 W

Product category

Accessories

Diameter

0 mm

Size

Front dimensions: 18 x 18 mm

Lens color

Gray

Design

Flat

Lens shape

Square



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia