



Chemical protection

ALTO 260

Prolonged contact (or immersion) | intermittent wear



CHEMICAL PROTECTION
TYPE A



CATEGORY 3



0334

DEXTERITY

EN420:
5/5

A good choice when dexterity and chemical protection is needed for extended wear

SPECIFIC ADVANTAGES



Comfort

- Added comfort and absorption of perspiration, due to the cotton flock-lining



Productivity

- Good grip on slippery objects, due to the embossed texture



Skin protection

- Good protection against chemical products



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- Optimised individual packaging to limit plastic waste
- Recycled material in the packaging: 30 %

INDUSTRIES

- Chemical industry
- Aeronautics industry
- Other industries

APPLICATIONS

- Work with composite materials (resins)
- Common handling Tasks
- Resin and adhesive manufacturing
- Resin-working
- Maintenance in wet environments



Chemical protection

ALTO 260

Prolonged contact (or immersion) | intermittent wear

LEGENDS

| | |
|-----------------------|---------------------------------------|
| EN388 | MECHANICAL HAZARDS |
| | PERFORMANCE LEVELS (X = NOT TESTED) |
| 2 1 2 0 X | |
| 0-4 0-5 0-4 0-4 A-F P | |
| | Impact protection (optional) |
| | Cut resistance according to ISO 13997 |
| | Puncture resistance |
| | Tear resistance |
| | Blade cut resistance |
| | Abrasion resistance |
| EN ISO 374-1 | CHEMICAL RISKS |
| | A: Methanol |
| | K: Sodium hydroxide 40% |
| | L: Sulphuric acid 96% |
| | M: Nitric acid 65% |
| | P: Hydrogen peroxide 30% |
| | T: Formaldehyde 37% |
| TYPE A | |
| EN ISO 374-5 | MICRO-ORGANISMS |
| | Protection against bacteria and fungi |

PRODUCT DETAILS

| | |
|---|-------------------------------|
| Interior finish | Flocked |
| Exterior finish | Embossed texture, chlorinated |
| Material | Natural latex |
| Cuff characteristic | Straight cuff |
| Colour.s | Black |
| Length (cm) | 32 |
| Thickness (mm) | 0.8 |
| European sizes | 7 8 9 10 11 |
| Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity) | 2.2E+12 Ω |
| Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity) | 3.6E+12 Ω |

LOGISTIC DETAILS

| | |
|-----------|---|
| Packaging | 1 pair/bag 10 pairs/bag 50 pairs/carton |
|-----------|---|

LEGISLATION

- This product is not classified as hazardous according to the directive 1999/45/EC of the European Parliament and of the Council.
- This product does not contain any substances of very high concern according to the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/18/1672
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France