

HC-M-08-GBIT-CT-F-SH - Contact insert module



1353610

<https://www.phoenixcontact.com/in/products/1353610>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 8, Socket, Crimp connection, 48 V, 5 A, 0.08 mm² ... 0.5 mm², application: Data, without crimp contacts, Shielded transmission to the module frame

Commercial data

Item number	1353610
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF7ACE
GTIN	4063151935795
Weight per piece (including packing)	51.8 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

Technical data

Notes

General	Connectors may be operated only when there is no load/voltage.
---------	--

Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

Product properties

Product type	Modular contact insert
Series	HC-M-08-GBIT
Application	Data
Sensor type	Ethernet
Number of positions	8
Connection profile	8
Contact numbering	1 - 8
No. of cable outlets	1
Number of module slots	1
Contact material type	turned
Shielded	yes

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection technology	Crimp connection
-----------------------	------------------

Conductor connection

Conductor cross section	0.08 mm ² ... 0.5 mm ²
Connection cross section AWG	28 ... 20
Stripping length of the individual wire	4.2 mm

Dimensions

Dimensional drawing	
Width	26.35 mm
Height	40.3 mm
Length	13.9 mm

HC-M-08-GBIT-CT-F-SH - Contact insert module



1353610

<https://www.phoenixcontact.com/in/products/1353610>

Mechanical characteristics

Contact diameter	1 mm
------------------	------

Electrical properties

Rated voltage (III/3)	48 V
Rated surge voltage	0.8 kV
Rated current	5 A
Transmission characteristics (category)	CAT6 _A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Au
Contact carrier material	PC


Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	including heating up of contacts
---------------------------------	----------------------------------


Drawings

Diagram



Derating diagram

Dimensional drawing



Female insert

HC-M-08-GBIT-CT-F-SH - Contact insert module



1353610

<https://www.phoenixcontact.com/in/products/1353610>

Classifications

ECLASS

ECLASS-13.0	27440218
-------------	----------

ETIM

ETIM 9.0	EC000438
----------	----------

HC-M-08-GBIT-CT-F-SH - Contact insert module



1353610

<https://www.phoenixcontact.com/in/products/1353610>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

HC-M-08-GBIT-CT-F-SH - Contact insert module



1353610

<https://www.phoenixcontact.com/in/products/1353610>

Accessories

HC-CBU-MOD - Coding element

1636130

<https://www.phoenixcontact.com/in/products/1636130>



Coding socket for coding up to 16 connectors, for HC Modular

HC-CST-MOD - Coding element

1636127

<https://www.phoenixcontact.com/in/products/1636127>



Coding peg for coding up to 16 connectors, for HC Modular

HC-M-08-GBIT-CT-F-SH - Contact insert module



1353610

<https://www.phoenixcontact.com/in/products/1353610>

CUC-DSC-J1BAU-S/DSC24 - D-SUB crimp contact

1418788

<https://www.phoenixcontact.com/in/products/1418788>



D-SUB crimp contact, connection method: Crimp connection, connection cross section: AWG 24- 20

CUC-DSC-J1BAU-S/DSC28 - D-SUB crimp contact

1418787

<https://www.phoenixcontact.com/in/products/1418787>



D-SUB crimp contact, connection method: Crimp connection, connection cross section: AWG 28- 24

HC-M-08-GBIT-CT-F-SH - Contact insert module

1353610

<https://www.phoenixcontact.com/in/products/1353610>



HC-M-B06-MFH-B - Module carrier frame

1182085

<https://www.phoenixcontact.com/in/products/1182085>



Module carrier frame, size: B6, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-M-B10-MFH-B - Module carrier frame

1182088

<https://www.phoenixcontact.com/in/products/1182088>



Module carrier frame, size: B10, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-M-08-GBIT-CT-F-SH - Contact insert module

1353610

<https://www.phoenixcontact.com/in/products/1353610>



HC-M-B16-MFH-B - Module carrier frame

1182090

<https://www.phoenixcontact.com/in/products/1182090>

Module carrier frame, size: B16, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-M-B24-MFH-B - Module carrier frame

1182094

<https://www.phoenixcontact.com/in/products/1182094>

Module carrier frame, size: B24, type : for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-M-08-GBIT-CT-F-SH - Contact insert module

1353610

<https://www.phoenixcontact.com/in/products/1353610>



HC-M-B06-MFH-H - Module carrier frame

1182087

<https://www.phoenixcontact.com/in/products/1182087>



Module carrier frame, size: B6, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-M-B10-MFH-H - Module carrier frame

1182089

<https://www.phoenixcontact.com/in/products/1182089>



Module carrier frame, size: B10, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame

HC-M-08-GBIT-CT-F-SH - Contact insert module

1353610

<https://www.phoenixcontact.com/in/products/1353610>



HC-M-B16-MFH-H - Module carrier frame

1182093

<https://www.phoenixcontact.com/in/products/1182093>

Module carrier frame, size: B16, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-M-B24-MFH-H - Module carrier frame

1182095

<https://www.phoenixcontact.com/in/products/1182095>

Module carrier frame, size: B24, type : for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², application: Module carrier frame



HC-M-08-GBIT-CT-F-SH - Contact insert module

1353610

<https://www.phoenixcontact.com/in/products/1353610>



HC-M-08-GBIT-CT-M-SH - Contact insert module

1353603

<https://www.phoenixcontact.com/in/products/1353603>



Contact insert module, number of positions: 8, Pin, Crimp connection, 48 V, 5 A, 0.08 mm² ... 0.5 mm², external cable diameter: 4.5 mm ... 9 mm, application: Data, without crimp contacts, Shielded transmission to the module frame

CRIMPFOX-TC MP - Crimping pliers with digital display

1212510

<https://www.phoenixcontact.com/in/products/1212510>



Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in