

DCS777T2-QW

XR FLEXVOLT 54V 2Ah Li-Ion Brushless Radial Miter Saw 216 mm



5054905003432



Product Description:

Blade Ø / Bore (mm): 216 / 30 No Load Speed (RPM): 6300 Head Tilt (°): 48 Miter Cuts L/R (°): 50 / 5090° Cutting Cap (H x W mm): 62 x 270 45° Cutting Cap (H x W mm): 48 x 190 XPS System: Projection of the Cutting Edge and Illumination of the Work Area

Product features and benefits:

- EXTENDED RUNTIME: 222 x 38mm x 68mm cuts in softwood on a single charge with a 6-inch FLEXVOLT battery integrated stops at 15°, 22.5°, 30° and 45° 3-YEAR WARRANTY: tools covered by an extended warranty, subject to registration
- FLEXVOLT XR 54V CORDLESS SYSTEM: wired power, XR FLEXVOLT BRUSHLESS MOTOR 54V: more power and of autonomy
- LARGE CUTTING CAPACITY: 60 mm x 270 mm at 90°
- CLASSIC DESIGN: inspired by the principle of the pull saw, improved and updated for the modern user COMPACT DESIGN: compact
- internal rail for high cutting capacity in an easily transportable format
- MACHINED BASE AND FENCE: designed, machined and controlled to meet the highest standards of precision LEFT-HAND SLIDING STOP: graduated, for better
- Material holding and guidance
- XPS SHADOWLINE CUT INDICATOR: allows for a fast and accurate blade alignment with no adjustment AIRLOCK
- SYSTEM: Compatible with the AirLock suction connection system, for easy, quick and secure connection

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration Ah POSITIVE STOPS:

Included Items:

- Batteries (x2) Charger (x1)
- 24-tooth carbide blade (x1)
- Service wrench (x1) Clamps
- (x1) Maximum cutting

Specifications techniques :

- [Imperial] Battery Capacity: 6.0 Ah
- Voltage: 54 V Weight (including battery): 16 Kg
- Blade bore: 30 mm
- Blade diameter: 216 mm
- Capacity (90°/45°) up 270 x 60 mm
 - Capacity cut (45°/90°): 190 x 60 mm Saw blade thickness: 2.16 mm
 - Capacity cutting Maximum (90°/45°): 270 x 48 mm Blade speed: 6300 rpm

- - capacity
(45°/45°):
190 x 48
mm