

Circular Saw XGT® , 40Vmax

HS012G

5 200 min⁻¹, 165 mm

Model HS012G is a 165mm (6-1/2") cordless circular saw powered by 40Vmax XGT® Li-Ion battery

Excellent combination of high power and lightweight design. Electric brake. AWS (Auto-start wireless system). Constant speed control.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	5200 min ⁻¹
Max. Cutting Depth at 90°	57 mm
Max. Cutting Depth at 45°	41 mm
Max. Bevel Range (Left)	0 - 50 °
AWS ready	✓
Sound Power Level (L _{WA})	102 dB(A)
Sound Pressure Level (L _{pA})	94 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	359 x 157 x 246 mm
Tool weight with battery	3,2 - 4,4 kg

User benefits

- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing