

Eaton 266031

Catalog Number: 266031

Eaton Moeller series NZM - Molded Case Circuit Breaker. Switch-disconnector 4p 1250A BG4



General specifications

Product Name	Catalog Number
Eaton Moeller series NZM switch-disconnector	266031
	EAN
	4015082660314
Product Length/Depth	Product Height
401 mm	207 mm
Product Width	Product Weight
280 mm	22 kg
Compliances	Certifications
RoHS conform	IEC
	IEC/EN 60947

Product specifications

Type

Switch-disconnector

Special features

Main switch characteristics including positive drive to IEC/EN 60204 and VDE 0113.

Isolating characteristics to IEC/EN 60947-3 and VDE 0660.

Busbar tag shroud to VDE 0160 Part 100.

Rated current = rated uninterrupted current: 1250 A

Application

Use in unearthed supply systems at 525 V

Amperage Rating

1250 A

Voltage rating

690 V - 690 V

Circuit breaker frame type

N4

Features

Version as maintenance-/service switch

Version as emergency stop installation

Motor drive optional

Version as main switch

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_N4](#)

Drawings

[eaton-circuit-breaker-nzm-mccb-dimensions-023.eps](#)

eCAD model

[DA-CE-ETN.N4-4-1250](#)

Installation instructions

[eaton-circuit-breaker-basic-unit-bg4-il012101zu.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CS-nzm4_4p](#)

[DA-CD-nzm4_4p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Intermediate mounting

Fixed

Built-in device fixed built-in technique

Ground mounting

Distribution board installation

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Equipment heat dissipation, current-dependent

173 W

Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

Rated short-time withstand current (Icw)

25 kA

Degree of protection

IP20 (basic protection type, in the area of the HMI devices)

Other

Direction of incoming supply

As required

Electrical connection type of main circuit

Bolt connection

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

40 °C

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

0

Protection against direct contact

Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part
263

Rated insulation voltage (Ui)

1000 V

Rated operating frequency

50 Hz

Rated operating power at AC-23, 400 V

710 kW

Rated operating power at AC-3, 400 V

0 kW

Switch positions

I, +, 0

Lifespan, mechanical

10000 operations

Overvoltage category

III

Rated operational current

1600 A (690 V AC-22/23A, making and breaking capacity)

1600 A (415 V AC-22/23A, making and breaking capacity)

Degree of protection (IP), front side

IP20

IP40 (with insulating surround)

IP66 (with door coupling rotary handle)

Degree of protection (terminations)

IP10 (tunnel terminal)

IP00 (terminations, phase isolator and band terminal)

Number of poles

Four-pole

Terminal capacity (copper strip)

Max. 10 segments of 50 mm x 1 mm (2x) at rear-side connection
(punched)

Min. 10 segments of 50 mm x 1 mm (2x) at rear-side connection
(punched)

Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor

terminal

10 segments of 50 mm x 1 mm (2x) at 1-hole module plate

Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal

10 segments of 80 mm x 1 mm (2x) at rear-side width extension

Handle color

Black

Lifespan, electrical

3000 operations at 400 V AC-1

3000 operations at 415 V AC-1

2000 operations at 400 V AC-3

2000 operations at 690 V AC-1

1000 operations at 690 V AC-3

2000 operations at 415 V AC-3

Functions

Voltage release optional

Interlockable

Disconnectors/main switches

Shock resistance

15 g (half-sinusoidal shock 11 ms)

Number of switches

1

Rated conditional short-circuit current (I_q)

0 kA

Rated conditional short-circuit current with back-up fuse

80 kA at 690 V

N4-630...1600: 2 x 800 AgGgL

100 kA at 400/415 V

Rated conditional short-circuit current with downstream fuse

N4-630...1600: 2 x 800 AgGgL

100 kA at 400/415 V

80 kA at 690 V

Rated operating voltage (U_e) at AC - max

690 V

Rated operational current for specified heat dissipation (I_n)

1250 A

Rated permanent current at AC-21, 400 V

0 A

Rated permanent current at AC-23, 400 V

0 A

Rated short-time withstand current (t = 0.3 s)

25 kA

Rated short-time withstand current (t = 1 s)

25 kA

Switching power at 400 V

0 kW

Handle type

Rocker lever

Number of operations per hour - max

60

Rated short-circuit making capacity I_{cm} at 690 V, 50/60 Hz

53 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

8000 V

Standard terminals

Screw terminal

Optional terminals

Connection on rear. Strip terminal. Tunnel terminal

Short-circuit protective device fuses - max

1600 A gL

Terminal capacity (copper busbar)

Min. 25 mm x 5 mm direct at switch rear-side connection

Min. 60 mm x 10 mm at rear-side width extension

Max. 80 mm x 10 mm (2x) at rear-side width extension

M10 at rear-side screw connection

Max. 50 mm x 10 mm (2x) direct at switch rear-side connection

Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate

50 mm x 10 mm (2x) at rear-side 2-hole module plate

Min. 25 mm x 5 mm at rear-side 1-hole module plate

Terminal capacity (copper solid conductor/cable)

95 mm² - 240 mm² (6x) at rear-side width extension

70 mm² - 185 mm² (2x) at rear-side 1-hole module plate

300 mm² (4x) at rear-side width extension

50 mm² (4x) at rear-side 2-hole module plate

50 mm² - 240 mm² (4x) at 4-hole tunnel terminal

185 mm² - 240 mm² (1x) at rear-side 1-hole module plate

35 mm² - 185 mm² (4x) at rear-side 2-hole module plate

Terminal capacity (aluminum solid conductor/cable)

240 mm² (2x) at rear-side width extension

70 mm² - 240 mm² (6x) at rear-side width extension

Terminal capacity (copper stranded conductor/cable)

120 mm² - 185 mm² (1x) direct at switch rear-side connection

50 mm² - 185 mm² (4x) direct at switch rear-side connection

Terminal capacity (aluminum stranded conductor/cable)

50 mm² - 240 mm² (4x) at 4-hole tunnel terminal



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia