



402.1687

INTERLOCKED SOCKET

16A 3P+N+E 6h 346-415V 50Hz 60Hz
130X260MM Screw terminals With mechanical interlock

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	ADVANCE GRP Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	INTERLOCKED SOCKET	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	INTERLOCKED SOCKET		
Rated current	16A		
Poles	3P+N+E	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Hour position	6h	EN 60309-2/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Rated voltage (range)	250-400V		
Rated voltage	346-415V	EN 60309-4 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Switched socket-outlets and connectors, with or without interlock
Working frequency	60Hz		
Working frequency	50Hz	DIRECTIVE LOW VOLTAGE 2014/35 /UE	[European Directives] Low Voltage Directive
Colour	RED		
Material	GRP Glass Reinforced Polyester		
Protection degree	Watertight		
Protection degree IP	IP66/IP67/IP69		
Protection degree IK	IK10		
Terminals	Screw terminals		
Flange	130X260MM		
Working temperature	-40°C/+60°C		

GLOW WIRE	GW 960°C
Self-extinguishing UL94	V0
Options	With mechanical interlock
Notes	WITHOUT FUSE HOLDER
Padlock	ø5mm