


HD MicroCamera





Camera unit for VideoFlex HD – ideal for very small openings

This camera unit for the VideoFlex HD is suitable for precise problem localisation in pipelines, wall cavities and motor vehicles. Detailed images and videos can be recorded with the high-resolution camera; these are then displayed on the display of the base unit any without loss of quality. Thanks to its extremely small diameter, the waterproof, petrol- and diesel-resistant camera head is ideal for small openings, and perfect for inspecting machinery, engines and confined areas. Thanks to the first-class object lighting provided by six high-performance LEDs, you can capture reliable images even in very poor conditions.

- Camera unit for the VideoFlex HD
- Effective problem localisation behind or in objects, walls, pipes, cavities
- Small camera head, ideal for places that are hard to reach
- Very detailed image and video capture using high-resolution camera and 1:1 reproduction on the display with no loss of quality
- 6 high-performance LEDs on the camera for powerful object lighting

TECHNICAL SPECIFICATIONS

DIAMETER CAMERA HEAD	3.9 mm
CAMERA RESOLUTION	1280 x 720 pixels
FIELD OF VIEW (FOV)	83°
DEPTH OF FOCUS (DOF)	3 ... 8 cm
LENGTH OF PROBE	2 m
PORTS	Industrial connector for camera
DIMENSIONS (W X H X D)	2080 mm x 21 mm x 21 mm
WEIGHT	96 g #



1280 x 720
pixel

LED
LIGHT

IP 68

