


Product datasheet

Specifications

PanelSeT SF Standard enlarged roof W700 x D800 mm



NSYRSF78L

Main

Range	PanelSeT
Offer type	Spare part
Accessory / separate part category	Enclosure accessory
Product or component type	Roof
Device application	Multi-purpose
Range compatibility	PanelSeT PanelSeT SF suitable enclosure
Device composition	1 roof

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - screw type M12 - roof fixing point location By screws - screw type M6 - roof fixing point location
Height	7.5 mm
Width	696 mm
Depth	796 mm
Thickness	1.5 mm
IP degree of protection	IP55 conforming to IEC 60529 (enclosure protection)

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	71.000 cm
Package 1 Length	81.000 cm
Package 1 Weight	7.900 kg
Unit Type of Package 2	PAM
Number of Units in Package 2	10
Package 2 Height	55.000 cm
Package 2 Width	100.000 cm
Package 2 Length	120.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	94.000 kg
------------------	-----------

Contractual warranty

Coverage	Core product
Warranty	18 months

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd
REACH Regulation	REACH Declaration

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No