





Part Number : 510896005
Product Description : 2.00mm Pitch Mi II System Wire-to-Board Crimp Housing, Dual Row, 60 Circuits, Gray
Series Number : 51089
Status : Not Recommended For New Design
Product Category : Connector Housings



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	51089
Description	2.00mm Pitch Mi II System Wire-to-Board Crimp Housing, Dual Row, 60 Circuits, Gray
Application	Signal, Wire-to-Board
Product Name	Mi II
UPC	800755527582

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	60
Color - Resin	Gray
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	2166.700/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C