

Product datasheet

Specifications



Acti9 iID - RCCB - 4P - 80A - 300mA - type AC

A9R82480

EAN Code: 3606480392757

❗ Discontinued

Main

Range	Acti9
product name	Acti9 iID
Product or component type	Residual current circuit breaker (RCCB)
Device short name	iID
Poles description	4P
Neutral position	Left
[In] rated current	80 A
network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC

Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	400...415 V AC 50/60 Hz
Residual current tripping technology	Voltage independent
Rated breaking and making capacity	Idm 1500 A Im 1500 A
Rated conditional short-circuit current	10 kA
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Surge current	250 A
Contact position indicator	Yes
control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	8
Height	96 mm
Width	72 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	74.5 mm
Net weight	0.37 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	AC-1: 10000 cycles
Locking options description	Padlocking device
Connections - terminals	Single terminal top or bottom 1...35 mm² rigid Single terminal top or bottom 1...25 mm² flexible Single terminal top or bottom 1...25 mm² flexible with ferrule
Wire stripping length	14 mm for top or bottom connection
Tightening torque	3.5 N.m top or bottom

Environment

Standards	GB 16916.21 EN/IEC 61008-1
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61008-1
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.2 cm
Package 1 Width	7.5 cm
Package 1 Length	10.0 cm
Package 1 Weight	380.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	27
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	10.747 kg


Contractual warranty

Warranty	18 months
----------	-----------


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)


[How we assess product sustainability >](#)

<div>Environmental footprint</div>	
Environmental Disclosure	Product Environmental Profile

Use Better

<div>Materials and Substances</div>	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	6cb0708f-a1ac-4da2-b46f-e46ba9165efa
REACH Regulation	REACH Declaration
China RoHS Regulation	China RoHS declaration

Use Again

<div>Repack and remanufacture</div>	
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product
Take-back	No