



DS7 soft starter, 110/230 V AC, 100 A



Powering Business Worldwide™

Part no. DS7-342SX100N0-N

Article no. 134938

Delivery programme

Function			Soft starters for three-phase loads
Mains supply voltage (50/60 Hz)	U _{LN}	V AC	200 - 480
Supply voltage			110/230 V AC
Control voltage	U _C		110 - 230 V AC
Rated operational current			
Device (AC-53)	I _e	A	100
Assigned motor rating			
at 400 V, 50 Hz	P	kW	55
at 480 V, 60 Hz	KP	HP	75
Derating factor class 20			0.55

Approvals

Product Standards

IEC/EN 60947-4-2; GB 14048.6; UL 508; CSA-C22.2 No 0-M91; CSA-C22.2 No 14-05 CE marking

NA Certification
Specially designed for NA
Suitable for
Current Limiting CB
Max. Voltage Rating
Degree of Protection

Request filed for UL and CSA
No
Branch circuits
No
480 V
IP20; UL/CSA Type 1

General

Standards			IEC/EN 60947-4-2
Climatic proofing			damp heat, constant, according to IEC 60068-2-3, damp heat, cyclic, according to IEC 60068-2-10
Ambient temperature		°C	-5 - +40°C up to 60°C at 2 % derating per Kelvin temperature rise
Ambient temperature, storage		°C	- 25 - 60
Altitude		m	0 - 1000 m, above that 1 % derating per 100 m , up to 2000 m
Mounting position			Vertical
Protection type			IP20
Degree of protection applies to the front/operating elements. Protection from all sides is IP00.			
Integrated			Protection type IP40 can be achieved on all sides with covers from the NZM range.
Protection against direct contact			Finger- and back-of-hand proof
Overvoltage category/pollution degree			II/2
Shock resistance			8 g/11 ms
Vibration resistance to EN 60721-3-2			2M2
Average heat dissipation at rated load cycle		W	25
Dimensions (W x H x D)		mm	45 x 150 x 118
Radio interference level			B
Weight		kg	1.8

Main conducting paths

Rated operating voltage	U _e	V AC	200 - 480
Supply frequency		Hz	50/60
Rated operational current	I _e	A	
AC-53 (motor loads)	I _e	A	100
Assigned motor rating (standard connection)			
at 230 V, 50 Hz	P	kW	30
at 400 V, 50 Hz	P	kW	55
200 V	KP	HP	30

at 230 V, 60 Hz	P	HP	30
at 480 V, 60 Hz	KP	HP	75
Overload cycle to IEC/EN 60947-4-2			
AC-53a (without bypass)			100

Terminal capacities

Cables (box terminal)			
Solid		mm ²	1 x (25 - 70) 2 x (6 - 25)
Stranded		mm ²	1 x (25 - 70) 2 x (6 - 25)
Solid or stranded		AWG	1 x (12 - 2/0)
Flat conductor		mm	
	min.	mm	2 x 9 x 0.8
	max.	mm	9 x 9 x 0.8
Control cables			
Solid		mm ²	1 x (0.5 - 2.5) 2 x (0.5 - 1.0)
Flexible with ferrule		mm ²	1 x (0.5 - 1.5) 2 x (0.5 - 0.75)
Stranded		mm ²	1 x (0.5 - 1.5) 2 x (0.5 - 1.0)
Solid or stranded		AWG	1 x (21 - 14) 2 x (21 - 18)
Tightening torque		Nm	0.4
Screwdriver (flat blade)		mm	0,6 x 3,5

Power section

Rated impulse withstand voltage	U _{imp}	kV	4
Rated insulation voltage	U _i	V AC	500
Short-circuit rating			
Type "1" coordination			
at AC-53a: 3...5 : 75...10			NZMN1-M100
Type “2” coordination short-circuit rating (additional with the fuses for coordination type “1”)			3 x 20.610.32-200
Fuse holders			3 x 21.313.02

Control circuit

Regulator supply voltage			
Voltage	U _s	V	120 - 15 % - 230 +10 %
Current consumption at no load 24 V DC		mA	35
Current consumption in operation at 24 V DC		mA	65
Current consumption at peak performance (close bypass) at 24 V DC		mA/ ms	600/50
Control voltage			
AC operated		V AC	120 - 15 % - 230 +10 %
Current consumption at 230 V DC		mA	14
Pick-up voltage		x U _s	
AC operated		V AC	108 - 120
Pick-up time			
AC operated		ms	250
Drop-out time			
AC operated		ms	190
Relay outputs			
Number			2 (TOR)
Voltage range		V AC	250
AC-1 current range		A	3 A, AC-1

Soft start function

Ramp times			
Acceleration		s	1 - 30

Deceleration	s	0 - 30
Start voltage (= turn-off voltage)	%	30 - 100
Voltage reduction at stop	%	
Voltage reduction at stop min.	%	8

Notes

Rated impulse withstand voltage:

- 1.2 μ s/50 μ s (rise time/fall time of the pulse to IEC/EN 60947-2 or -3)
- Applies for control circuit/power section/enclosure

Dimensions

