



Part Number : [2240851044](#)
Product Description : Mini-Fit Max-to-Mini-Fit
Max Off-the-Shelf (OTS) Cable Assembly, Dual
Row, Tin (Sn) Plating, 4 Circuits, 600.00mm
Length, Black
Series Number : 224085
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2240851044_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224085
Description	Mini-Fit Max-to-Mini-Fit Max Off-the-Shelf (OTS) Cable Assembly, Dual Row, Tin (Sn) Plating, 4 Circuits, 600.00mm Length, Black
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Max-to-Mini-Fit Max
Product Name	Mini-Fit Max
Type	Discrete Wire Assembly
UPC	196823397011

Electrical

Current - Maximum per Contact	20A
Voltage - Maximum	600V AC (RMS)

Physical

Cable Length	600.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	61.755/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag

Pitch - Mating Interface	4.20mm
Plating min - Mating	1.020µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Insulation Diameter	2.65mm
Wire Size (AWG)	14

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Max Vertical Dual Row Headers	<u>212520</u>