

0826543

https://www.phoenixcontact.com/gb/products/0826543

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Carrier for conductor marking collar, black, unlabeled, mounting type: Assembly with cable ties, cable diameter: > 16 mm, text field height: 10 mm, text field width: 100 mm

## Your advantages

- · The printed individual markers are pushed onto the corresponding holders
- · Cable markers for marking cables and conductors with larger cross sections

#### Commercial data

Item number	0826543
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG231A
Product key	BG231A
Catalog page	Page 245 (C-3-2019)
GTIN	4046356414517
Weight per piece (including packing)	1.324 g
Weight per piece (excluding packing)	1.276 g
Customs tariff number	39269097
Country of origin	SE



0826543

https://www.phoenixcontact.com/gb/products/0826543

# Technical data

## Product properties

Product type	Marker carrier cable
Туре	Marking strip/label

#### **Dimensions**

Width	10 mm
Length	100 mm

#### External dimensions

Outside diameter	> 16 mm 136 mm
------------------	----------------

#### Text field

Text field width	100 mm
Text field height	10 mm

## Material specifications

Color	black (RAL 9005)
Material	PVC

### Cable/line

External cable diameter > 16.00 mm
------------------------------------

## Environmental and real-life conditions

#### **UV** resistance

Specification	ISO 4892-2:2013-03 (following)	
Result	Test passed	
Test duration	96 h	

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07	
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)	
Isopropyl [CAS No. 67-63-0]	Test passed	
n-Hexane [CAS No. 110-54-3]	Test passed	
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed	

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2



0826543

https://www.phoenixcontact.com/gb/products/0826543

90	Iŧ.	cn	rav	test
Sa	ш	SD	ıαv	iesi

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed
Ambient conditions	
Ambient temperature (operation)	-30 °C 70 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)
tandards and regulations	
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
ounting	
Mounting type	Assembly with cable ties



0826543

https://www.phoenixcontact.com/gb/products/0826543

# Classifications

## **ECLASS**

	ECLASS-11.0	27281102	
	ECLASS-12.0	27281102	
	ECLASS-13.0	27281102	
ETIM			
	ETIM 9.0	EC001530	
UNSPSC			
	UNSPSC 21.0	39131500	



0826543

https://www.phoenixcontact.com/gb/products/0826543

# Environmental product compliance

#### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
EU REACH SVHC  REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk