



GEE62FR-CY Slotted Grommet, Natural, FR PE, 0.06" Max Panel, PK1

GEE62FR-CY

Slotted grommet edging, .062" thickness, flame retardant polyethylene, natural, 100 ft.

Specifications

Product Type	Slotted Grommet Edging
Color	Natural
Flammability Rating	UL94V-0
Material	Polyethylene
Maximum Compatible Panel Thickness (In.)	0.06
Maximum Compatible Panel Thickness (mm)	1.6
Minimum Compatible Panel Thickness (In.)	0.036
Minimum Compatible Panel Thickness (mm)	0.9
Maximum Operating Temperature (°C)	50
Maximum Operating Temperature (°F)	122
Minimum Operating Temperature (°C)	-20
Minimum Operating Temperature (°F)	-4
Overall Length (ft.)	100
Overall Length (m)	30.48
Overall Width (In.)	0.13
Overall Width (mm)	3.3
Overall Height (In.)	0.16
Overall Height (mm)	4.1
Resistance Properties	Flame-Retardant
Standards Met	RoHS Compliant
Application	To Protect and Prevent Wires and Cables from Chafing Against Sharp Edges of Panel Walls and Knockouts.
Part Features	Provides protection for cables being installed where there might be sharp edges with irregular shaped and round panel holes.

Packaging Detail

UPC	07498310754
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.2202
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000