

BASIC FRAME NS1600H 4P 1600 FXD Man.

Circuit breaker frame, ComPacT NS1600H, 70kA at 415VAC, 1600A, 4P, fixed, manually operated, without control unit

Main

Range	ComPacT
Range of product	ComPacT NS630b...1600 new generation
Product or component type	Basic frame
Device application	Distribution
Number of poles	4P
Neutral position	Left
[In] rated current	1600 A at 50 °C
[Ue] rated operational voltage	690 V AC 50/60 Hz
Network type	AC
Network frequency	50/60 Hz
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Utilisation category	Category B
[Icu] rated ultimate short-circuit breaking capacity	85 KA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 70 KA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 65 KA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 50 KA Icu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 42 KA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
Performance level	H 70 kA 415 V AC
Control type	Manually operated
Mounting mode	Fixed






Complementary

[Ui] rated insulation voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	8 kV conforming to IEC 60947-2
[Ics] rated service short-circuit breaking capacity	37 KA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 37 KA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 37 KA at 440 V AC 50/60 Hz conforming to IEC 60947-2 30 KA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 22 KA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] rated short-time withstand current	19.2 kA 1 s conforming to IEC 60947-2
Integral instant protection	40 kA
Mechanical durability	10000 cycles conforming to IEC 60947-2
Electrical durability	1000 Cycles 690 V AC 50/60 Hz In conforming to IEC 60947-2 2000 Cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-2 2000 Cycles 440 V AC 50/60 Hz In conforming to IEC 60947-2 5000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-2
Power losses	74 W
Mounting support	Backplate
Connection pitch	70 mm
Protection type	Without protection
Height (H)	327 mm
Width (W)	280 mm
Depth (D)	147 mm

Environment

Standards	IEC 60947-2
Product certifications	IECEE CB Scheme
Pollution degree	3 conforming to IEC 60947
IP degree of protection	IP40 conforming to IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	76c2e213-3b51-4d8b-afdf-632ded42d731
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Product contains halogen above thresholds
Silicon free	No
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	1564