


Rated Cross-Section 1.5 mm²



PM 5.08/90



Technical data		VDE	UL	CSA
Rated voltage	V*	250	300	300
Rated current	A	17.5	10	10
Clamping range max.	mm ² /AWG	1.5	14	14



*Pollution severity 3 / Overvoltage category III
Additional technical data see page 58

Pin length **3.5 mm** **3.5 mm**

Colour

Poles	Type	Cat.No.	Cat.No.	Qty.
2	PM 5.08/2/90	176049	176051	500
3	PM 5.08/3/90	176050	176052	500

MK8/135



Technical data		VDE	UL	CSA
Rated voltage	V*	60	50	150
Rated current	A	16	15	10
Clamping range max.	mm ² /AWG	1.5	14	14



*Pollution severity 3 / Overvoltage category III
Additional technical data see page 59

Pin length **5.0 mm**

Colour

Poles	Type	Cat.No.	Cat.No.	Qty.
2	MK 8/2	033206		200
3	MK 8/3	030786		100
4	MK 8/4	030776		100
10	MK 8/10	030266		50

MK7.5/135



Technical data		VDE	UL	CSA
Rated voltage	V*	250	300	300
Rated current	A	16	10	10
Clamping range max.	mm ² /AWG	1.5	16	16

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 59

Pin length **5.0 mm**

Colour

Poles	Type	Cat.No.	Cat.No.	Qty.
3	MK 7.5/3	037926		100

Accessories	Page
Marking	44
Fixing	-
Miscellaneous	47

Accessories	Page
Marking	44
Fixing	-
Miscellaneous	47



Accessories	Page
Marking	44
Fixing	-
Miscellaneous	47



Rated Cross-Section 1.5 mm²



LM 3.5/90



Technical data		VDE	UL	CSA
Rated voltage	V*	125	300	300
Rated current	A	12	10	10
Clamping range max.	mm ² /AWG	1.5	14	14



*Pollution severity 3 / Overvoltage category III
Additional technical data see page 60

Pin length 3.2 mm 4.5 mm



Colour				
Poles	Type	Cat.No.	Cat.No.	Qty.
2	LM 3.5/2/90	166775	169967	100
3	LM 3.5/3/90	166777	169968	100

LM1N 3.5/90



Technical data		VDE	UL	CSA
Rated voltage	V*	125	300	300
Rated current	A	10	10	10
Clamping range max.	mm ² /AWG	1.5	14	14




*Pollution severity 3 / Overvoltage category III
Additional technical data see page 60

Pin length 3.2 mm 4.5 mm



Colour				
Poles	Type	Cat.No.	Cat.No.	Qty.
2	LM1N 3.5/2	171671	174738	100
3	LM1N 3.5/3	171672	174739	100

LM 3.5/135



Technical data		VDE	UL	CSA
Rated voltage	V*	125	300	300
Rated current	A	12	10	10
Clamping range max.	mm ² /AWG	1.5	14	14

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 60

Pin length 3.2 mm 4.5 mm



Colour				
Poles	Type	Cat.No.	Cat.No.	Qty.
2	LM 3.5/2/135	171498	171501	100
3	LM 3.5/3/135	171502	171505	100

Attention: Customers are advised to ensure support for LM1N on the PCB.

Accessories	Page
Marking	44
Fixing	-
Miscellaneous	47

Accessories	Page
Marking	44
Fixing	-
Miscellaneous	47

Accessories	Page
Marking	-
Fixing	-
Miscellaneous	-

