



EASY-TO-USE CONTROLS



WHEEL-MOUNTED STEEL FRAME
FOR OUTSTANDING MOBILITY



SWIVEL DRUM FOR DIRECTIONAL AIRFLOW



PULL HANDLE FOR EASY MOVEMENT

ITEM. 05638

SIP 36" INDUSTRIAL DRUM FAN

HEAVY-DUTY DRUM FAN FOR POWERFUL INDOOR AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 36" Industrial Drum Fan** delivers powerful, variable speed airflow to help cool spaces and freshen stale air in a variety of industrial environments.

Wheel-mounted on a cradled steel frame, the drum enclosed, heavy-duty 3-blade fan can be rotated between 360° on its vertical axis to maximise air circulation and coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 410w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

2 settings for variable fan speed:

- **Speed Setting 1:** 860rpm
- **Speed Setting 2:** 950pm

✓ DYNAMIC AIRFLOW FUNCTION

The adjustable tilting fan head can be rotated 360° on it's vertical axis for greater airflow coverage.

THIS PRODUCT COMES WITH AN SIP 2-YEAR SILVER WARRANTY*

FIND OUT MORE AT [SIP-GROUP.COM/WARRANTY](https://www.sip-group.com/warranty)



ITEM. 05638

SIP 36" INDUSTRIAL DRUM FAN

FEATURES & BENEFITS CONT.

✔ OUTSTANDING MOBILITY

The wheel-mounted cradled steel frame is fitted with pull handles which allows the fan to be easily moved between locations for use.

✔ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.

A robust and balanced steel frame maintains fan stability when in use.

APPLICATIONS & USES

**DELIVERS POWERFUL VARIABLE SPEED
AIR CIRCULATION TO INDOOR SPACES**

**PERFECT FOR INDUSTRIAL, COMMERCIAL
& AGRICULTURAL WORKSHOP AREAS**

ITEM NO.	05638	
INPUT SUPPLY	230v (13A)	
MOTOR POWER	410w (0.55hp)	
POWER CABLE	240cm	
FAN DIAMETER	Ø 36" (915mm)	
SPEED SETTINGS	2 speed settings	
	Speed Setting 1	Speed Setting 2
	860rpm	950rpm
NOISE LEVEL	84dB(A)	
NET WEIGHT	27kg	
GROSS WEIGHT	30.55kg	
PRODUCT DIMENSIONS	1255(H) x 980(W) x 295mm(D)	
PACKAGED DIMENSIONS	1095(H) x 1095(W) x 315mm(D)	