

Technical data


NU1011

Single row cylindrical roller bearings



Single row cylindrical roller bearing, floating, separable, brass cage

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	55 mm
D - External diameter	90 mm
B - Bearing/Inner ring width	18 mm
E - Upper roller diameter	80,5 mm
F - Under roller diameter	64,5 mm
rs - Min fillet radius	1,1 mm
r1s - Min fillet radius	1 mm
Radial clearance class	CN
Mass	0,442 kg

PRODUCT PERFORMANCE

C - Dynamic load	42000000 mN
C0 - Static load	44000000 mN
Cu - Fatigue limit load	5350000 mN
N lim - Oil lubrication limit speed	58200 °/s
N lim - Grease lubrication limit speed	49200 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	60 mm
da max - Small face shoulder max diameter	63 mm
db min - Min inner ring GO diameter	66 mm
Da max - Max shoulder diameter OR	83,5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

ABUTMENT	
ra max - Max fillet radius	1 mm
r1a - Max fillet radius	1 mm

INDUSTRY CALCUL FACTORS	
Equivalent dynamic radial load	
$P = Fr$	
Equivalent static radial load	
$P_0 = Fr$	