

## Crimpflange set



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 21 01 010 0024                                                                |
| Specification      | Crimpflange set                                                               |
| HARTING eCatalogue | <a href="https://harting.com/21010100024">https://harting.com/21010100024</a> |

### Identification

|                   |                         |
|-------------------|-------------------------|
| Category          | Accessories             |
| Series            | Circular connectors M12 |
| Identification    | Slim Design             |
| Type of accessory | Crimp flange set        |

### Version

|         |                                                                                                               |
|---------|---------------------------------------------------------------------------------------------------------------|
| Details | HARTING offers to test and define the best crimp flange and ferrule combination for customer specific cables. |
|---------|---------------------------------------------------------------------------------------------------------------|

### Technical characteristics

|                     |                |
|---------------------|----------------|
| Ambient temperature | -40 ... +85 °C |
|---------------------|----------------|

### Material properties

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| RoHS                                 | compliant with exemption                               |
| RoHS exemptions                      | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                           | compliant with exemption                               |
| China RoHS                           | 50                                                     |
| REACH Annex XVII substances          | Not contained                                          |
| REACH ANNEX XIV substances           | Not contained                                          |
| REACH SVHC substances                | Yes                                                    |
| REACH SVHC substances                | Lead                                                   |
| ECHA SCIP number                     | 0d7d3693-d625-47ab-934a-d241bf72c86e                   |
| California Proposition 65 substances | Yes                                                    |



Pushing Performance  
Since 1945

Material properties

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| California Proposition 65 substances | Lead                                |
|                                      | Nickel                              |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) + A1 (2023-10) |
| Requirement set with Hazard Levels   | R22 (HL 1-3)                        |
|                                      | R23 (HL 1-3)                        |

Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 1                                          |
| Net weight                     | 7.5 g                                      |
| Country of origin              | Romania                                    |
| European customs tariff number | 85366990                                   |
| GTIN                           | 5713140236301                              |
| eCl@ss                         | 27440292 Connector component (accessories) |
| ETIM                           | EC002943                                   |
| UNSPSC 24.0                    | 39121400                                   |