

Safety transformer, 16VA Primary 230 V AC, 50Hz, secondary 8 V AC With PTC fuse, 2MW++



Model	
product brand name	SENTRON
product designation	Safety transformer
design of the transformer	Safety transformer
General technical data	
supplied active power / maximum	16 W
Voltage	
input voltage	230 V
output voltage	8 V
• _1 / rated value	8 V
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	7 W
Current	
output current	
• maximum	2 A
• _1 / rated value	2 A

## Suitability

suitability for integration

- surface-mounted installation
- flush mounting

No

No

## Product details

product component / switch

No

## Product function

product function / thermal protection

Yes

## Inputs Outputs

property of the output / short-circuit proof

Yes

## Mechanical Design

height

64 mm

width

36 mm

length

90 mm

number of width units

2

mounting type / side-by-side mounting

Yes

## Certificates

**Declaration of Conformity**

**other**

[Confirmation](#)



EG-Konf.

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=4AC3716-0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/4AC3716-0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=4AC3716-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=4AC3716-0)

**Cx-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

