


# Actuator

704.102.01

Distribution by  
Rs-online



<https://rs-online.eao.com/p/704.102.01>

Your product:

---



## 704.102.01 Actuator

### FRONT

|                       |         |
|-----------------------|---------|
| Front dimension:      | Ø 29 mm |
| Front form:           | Round   |
| Front bezel colour:   | Grey    |
| Front bezel material: | Plastic |

### MOUNTING

|                |                |
|----------------|----------------|
| Design:        | Raised         |
| Mounting type: | Panel mounting |

### OPERATING-/INDICATION PART

|                   |         |
|-------------------|---------|
| Lever colour:     | Black   |
| Lever bar colour: | Yellow  |
| Lever material:   | plastic |
| Lever shape:      | long    |

### ELECTRICAL CHARACTERISTICS

|            |                                                                                           |
|------------|-------------------------------------------------------------------------------------------|
| Standards: | The switches comply with the "Standards for low-voltage switching devices" DIN EN 60947-1 |
|------------|-------------------------------------------------------------------------------------------|

### MECHANICAL CHARACTERISTIC

|                      |                  |
|----------------------|------------------|
| Switching action:    | Rest - Momentary |
| Switching positions: | 2 positions      |
| Switching angle:     | 42° right        |

**Mechanical lifetime:** ≤2.5 Mil. cycles of operation

**Weight:** 0.034 kg

## AMBIENT CONDITION

**IP Protection:** IP65 front side

**Storage temperature:** – 40 °C ... + 85 °C

## CERTIFICATE

**REACH:** REACH compliant

**RoHS:** RoHS compliant


## OTHER

**Short Description:** Actuator, Ø 29 mm, optional illuminative, Black, long, Round, Grey, Plastic, Rest - Momentary

**Hints:** Max. 3 switching elements can be clipped on

**max. number of switching elements:** 3


**Switching positions:**



**Wiring diagrams:**



**Mounting cut-outs:**




A = Screw terminal

B = Push-in terminal (PIT)

C = Plug-in terminal 6.3 mm x 0.8 mm

D = Double plug-in terminal 6.3 mm x 0.8 mm

**Dimension drawings:**



A = Screw terminal