

Angle Drill LXT®

DDA460

18V X2 • 136 Nm • 0 – 1 400 min⁻¹

Angle drill with brushless motor for heavy-duty use

An angle grinder with two speed ranges for extremely heavy-duty jobs, such as drilling large holes in wood. The tool runs on two 18V LXT® batteries that achieve a voltage of 36V. Max. torque of 136 Nm.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 350 / 1400 min ⁻¹
Max. Drilling Diameter in Wood	159 mm
Max. Drilling Diameter in Steel	13 mm
Driving Shank	20UNF / 1/2 "
Drill Chuck Capacity	1,5 - 13 mm
Angle length	133 mm
Max. Torque (2. Gear / 1. Gear)	48 / 136 Nm
Drilling Capacity Wood (Auger Bit)	50 mm
Drilling Capacity Wood (Self-feed bit)	65 / 118 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Power Level (L _{WA})	96 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Reversing switch
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low
- Powerful drilling even large diameter holes

Link to product - www.makitaauk.com



Related products

Optional AC

783203-8

Hex Wrench 5 Mm

783204-6

Hex Wrench 6Mm

Other

User manual

Parts drawing