

Endress+Hauser FTL41-BBA8AAAAA1AJI1VBJ

Compact point level switch for liquids in basic applications. The Liquiphant FTL41 is used for overflow prevention or as pump dry-run protector. It is suitable for level limit detection.



Picture for reference only. Product appearance may vary based on configuration

The Liquiphant FTL41 is a vibronic point level switch for liquids. It is simple to use thanks to the active sensor technology and does not need adjustment to different media.

Configuration of FTL41-BBA8AAAAA1AJI1VBJ:

Approval:	BB	ATEX/IEC II 1/2G, 2G Ex ia IIC T6 Ga/Gb
Output:	A8	FEL48, 2-wire NAMUR
Display; Operation:	A	W/o; switch
Housing; Material:	A	Single compartment; plastic
Electrical Connection:	A	Gland M20, plastic, IP66/68 NEMA Type 4X/6P
Application:	A	Process max 150oC/302oF, max 40bar
Surface Refinement:	A	Standard Ra<3,2µm/126µin
Type Of Probe:	1	Compact version
Sensor Length; Material:	AJ	Compact version; 316L
Process Connection, Sealing Surface:	I1	Thread ISO228, G
Process Connection:	VBJ	3/4", 316L

Alternative part number: FTL41-1530/0