


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

19


BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
FT	60	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REV & REDRAW ON CAD PER EC 0320-70-97	11 MAR 97	-	-



1. ALL DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. COPPER ALLOY.
3. 2.54μm [0.001000] MIN TIN.
4. WIRE BARREL WILL ACCEPT ONE 10 OR 12 AWG STRANDED WIRE OR COMBINATIONS OF 12,18,16 AND 14 AWG WIRE.
5. THIS TERMINAL IS USED WITH HOUSING 556137 AND MOUNTING ADAPTER 557313-1.
6. APPLICATOR REEL: 567256-3 FOR "T" TERMINATOR, 567256-4 FOR AMP-O-ELECTRIC™ MODEL "K" MACHINE 565435-5.
7. HAND TOOL-LOOSE PIECE.

200 TERMINALS PER BOX	LOOSE PIECE	556136-2
2000 TERMINALS ON 24" DIA REEL	ON STRIP	556136-1
PACKAGING	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M.BINNER 11 MAR 97		AMP AMP Incorporated Harrisburg, PA 17105-3608					
DIMENSIONS: mm [INCHES]			CHK R.STONE 14 MAR 97							
			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.McALONIS 17 MAR 97			NAME TERMINAL, 12-10 AWG, FOLDED CRIMP, WTW, AMPINNERGY™		
			0 PLC ±-		PRODUCT SPEC					
			1 PLC ±-		108-1373					
			2 PLC ±-		APPLICATION SPEC					
MATERIAL 2			3 PLC ±-		SIZE		CAGE CODE		DRAWING NO	
			4 PLC ±-		114-6051		A2		00779	
ANGLES ±-			FINISH 3		WEIGHT -		C-556136		SCALE 5:1	
CUSTOMER DRAWING							SHEET 1 OF 1		REV A	