

## 3317HL.B



### Models Versions

3317HL.B	black w/foam
3317HL.BE	black empty
3317HL.G	mil. green w/foam
3317HL.GE	mil. green empty
3317HL.O	orange w/foam
3317HL.OE	orange empty

- Made of Copolymer Polypropylene compound
- Waterproof, resistant to chemicals, humidity, dust
- Resistant to harsh temperatures (-33°C / +90°C)
- Jam-free purge valve and latches
- Recommended for professional applications

- 100% made in Italy: Italian design and proven functionality
- First to achieve the new military standard qualifications
- Recognized as the most versatile case to customize
- Widest choice of accessories to customize your experience
- Incorporate a number of patented innovations

Technical Features		L	W	D		
		Length	Width	Depth	Lid	Base
Internal dim.	mm	330	234	170	68	102
External dim.	mm	360	304	192		
Weight empty				Kg 1,86		
Weight w/foam				Kg 2,08		
Weight w/multi				Kg ---		
Volume				lt 13,1		
Buoyancy				Kg/max 7,1		
Temp. rating				°C min -33 max +90		
Certifications						
2002/95/EC Conformity with the Directive 2002/95/EC						
DEF STAN 81-41 (level J)						
IP67 Dustproof - Waterproof						
STANAG 4280 (edition 2)						

