

HONEYWELL MILLER MB FULL BODY SAFETY HARNES

Designed to provide your team with superior protection, Honeywell Miller MB Full Body Safety Harness provides the mobility with optimum comfort for long periods of use. It has a lightweight anti-corrosion dachrotized steel single rear dorsal D-ring, a cushioned back pad, and a durable and adjustable polyamide webbing strap that perfectly fits ASEAN sizes.



FEATURES & BENEFITS

- Lightweight, high corrosion resistance dachrotized steel single fall arrest dorsal D-ring and matting buckles.
- Comfortable cushioned back pad.
- Durable 44mm polyamide webbing strap.
- One-size-fits-all, for ASEAN sizes – S, M & L.
- Easy-to-wear harness.
- 3 adjustment points – Pass-thru buckles on chest and leg straps.
- Yellow and black colored strap for greater visibility from a distance and in dark environments.
- Maximum working load up to 100kg.

REF.	DESCRIPTION	WEIGHT	UOM
MB9000	Full Body Harness, 1 Back D-Ring	750g	PC



CERTIFICATIONS

- EN 361:2002
- Singapore PSB SS528: Part 6: 2006
- Malaysia SIRIM



APPLICATION

Suitable for fall arrest application in construction industry and for general works at height.

For more information

www.honeywellsafety.com

Honeywell Personal Protective Equipment

Malaysia (Asia Pacific Headquarters)

Level 25, UOA Corporate Tower,
Lobby B, The Vertical, Bangsar South
City, 59200 Kuala Lumpur, Malaysia

Phone: +603-2777 3948 / 3950

Email: hsp.asean@Honeywell.com

Singapore: +65 6714 6800

Indonesia: +62 21 2964 0328

Philippines: +632 730 7300

Thailand: +66 2 693 3099

Vietnam: +84 28 5411 2260

Harness-DS | Rev01 | 11/20
© 2020 Honeywell International Inc.

THE
FUTURE
IS
WHAT
WE
MAKE IT

Honeywell