

Eaton 132774

Catalog Number: 132774

Eaton Moeller series xEffect - FAZ-NA, FAZ-RT MCB. FAZ-RT, 3-pole, tripping characteristic: B, rated current In: 5 A



General specifications

Product Name

Eaton Moeller series xEffect - FAZ-NA,
FAZ-RT MCB

Catalog Number

132774

EAN

4015081297238

Product Length/Depth

105 mm

Product Height

75.5 mm

Product Width

53.1 mm

Product Weight

0.371 kg

Compliances

RoHS conform

Certifications

North America (UL listed, CSA certified)

UL (File No. E235139)

CSA (Class No. 1432-01)

UL (Category Control Number DIVQ)

Specially designed for North America,
suitable as BCPD

IEC 60947-2

CSA (File No. 204453)

CE marking

IEC/EN 60947-2

CSA-C22.2 No. 5-09

UL 489, CSA C22.2 No. 5

UL 489

EN45545-2

IEC 61373

Delivery program

Application

Feeder circuits, branch circuits
Switchgear for industrial and advanced commercial applications
xEffect - Switchgear for industrial and advanced commercial applications

Number of poles

Three-pole

Number of poles (total)

3

Number of poles (protected)

3

Tripping characteristic

B

Release characteristic

B

Amperage Rating

5 A

Type

FAZ-RT
Miniature circuit breaker

Technical data - electrical

Voltage type

AC

Voltage rating

277 V AC / 480 V AC

Voltage rating at DC

60 V DC

Voltage rating (IEC/EN 60947-2)

440 V

Voltage rating (UL)

480Y/277 V

Rated operational voltage (Ue) - max

415 V

Rated insulation voltage (Ui)

440 V

Rated impulse withstand voltage (Uimp)

4 kV

Frequency rating - min

50 Hz

Frequency rating - max

60 Hz

Rated switching capacity (IEC/EN 60947-2)

15 kA

Breaking capacity

10 kA (UL489)

Rated short-circuit breaking capacity (EN 60898) at 230 V

0 kA

Rated short-circuit breaking capacity (EN 60898) at 400 V

0 kA

Rated short-circuit breaking capacity (IEC 60947-2) at 230 V

15 kA

Rated short-circuit breaking capacity (IEC 60947-2) at 400 V

15 kA

Selectivity class

3

Overvoltage category

III

Pollution degree

2

Lifespan, electrical

20000 operations

Direction of incoming supply

As required

Technical data - mechanical

Frame

45 mm

Enclosure width

105 mm

Width in number of modular spacings

3

Built-in depth

70.5 mm

Mounting width per pole

17.7 mm

Mounting width

17.7 mm

Mounting Method

Top-hat rail IEC/EN 60715

Mounting position

As required

Degree of protection

IP40 (when fitted)

IP20

IP20 (IEC)

UL/CSA Type: -

Terminals (top and bottom)

Twin-purpose terminals

Connectable conductor cross section (solid-core) - min

1 mm²

Connectable conductor cross section (solid-core) - max

25 mm²

Connectable conductor cross section (multi-wired) - min

1 mm²

Connectable conductor cross section (multi-wired) - max

25 mm²

Terminal protection

Finger and hand touch safe, DGUV VS3, EN 50274

Tightening torque

UL: 4 Nm (36 lb-in) for AWG 6

Max. 2.4 Nm

UL: 2.4 Nm (21 lb-in) for AWG 18 - AWG 12
UL: 2.8 Nm (25 lb-in) for AWG 10 - AWG 8

Design verification as per IEC/EN - technical data

Rated operational current for specified heat dissipation (In)
5 A

Heat dissipation per pole, current-dependent
0 W

Equipment heat dissipation, current-dependent
5.5 W

Static heat dissipation, non-current-dependent
0 W

Heat dissipation capacity
0 W

Ambient operating temperature - min
-25 °C

Ambient operating temperature - max
75 °C

Design verification as per IEC/EN 61439

10.2.2 Corrosion resistance
Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures
Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat
Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects
Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation
Meets the product standard's requirements.

10.2.5 Lifting
Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact
Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions
Meets the product standard's requirements.

Additional information

Current limiting class
3

Features
Additional equipment possible

Functions
Current limiting circuit breaker

Special features
Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity

Used with
FAZ-RT
Miniature circuit breaker

Resources

Brochures
[eaton-pdd-railrolling-stock-brochure-br011002en-en-us.pdf](#)

Catalogs
[eaton-xeffect-faz-na-rt-mcb-catalog-ca003032en-en-us.pdf](#)

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Characteristic curve

[eaton-xeffect-faz-na,-mcb-dimensions-003.jpg](#)

[eaton-xeffect-faz-na,-mcb-characteristic-curve.jpg](#)

[eaton-xeffect-faz-na,-mcb-characteristic-curve-002.jpg](#)

Declarations of conformity

[DA-DC-03_FAZ-RT](#)

[DA-DC-03_FAZ-B-C-D](#)

Drawings

[eaton-xeffect-faz-na,-mcb-dimensions.jpg](#)

[eaton-mcb-xeffect-faz-na,-3d-drawing-002.eps](#)

eCAD model

[DA-CE-ETN.FAZ-B5_3-RT](#)

Installation instructions

[IL019133ZU](#)

mCAD model

[DA-CD-faz_na_3p](#)

[DA-CS-faz_na_3p](#)

Wiring diagrams

[eaton-mcb-xeffect-faz-na,-wiring-diagram-002.eps](#)

[eaton-xpole-mm4-6-m-mcb-wiring-diagram-005.jpg](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)