








CAPPED VIEW



REAR VIEW



RECOMMEND MINIMUM MOUNTING PITCH



RECOMMEND PANEL CUT OUT

PART NUMBER	CONTACT FINISH
AXS5MP2	TIN PLATED
AXS5MP2-AU	GOLD PLATED

NOTE:
1. MATING CONNECTOR SHELL TO HAVE MIN 1.6 SURFACE FINISH TO ACHIEVE IP54 RATING OF THIS CONNECTOR.
2. BLACK MOUNTING SCREW 52500011-430 x 4 PCS TO BE SUPPLIED WITH THE CONNECTOR, MAX TORQUE 0.5Nm.
3. DUE TO 0.4mm THICK RUBBER SEAL, THE DIM WILL VARY DEPENDING ON THE SCREWS TIGHTENING IN ASSEMBLY.

3	52730035-000	AXS FRONT FLANGE D TYPE RUBBER SEAL IP54 WITH CAP	1
2	52500011-430	SCREW 2.9 x 1.06mm USED FOR PLASTIC MATERIAL	4
1	55011499-025/925	AXS5MP2 WITHOUT RUBBER FLANGE - TIN/GOLD PLATED CONTACT	1
ITEM	PART NUMBER	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE	
LINEAR	ANGULAR
X ± 0.5	X' ± 1
X.X ± 0.2	X.X' ± 30'
X.XX ± 0.1	X.XX' ± 15'

BREAK ALL SHARP EDGES
AND REMOVE ALL BURRS

DO NOT SCALE

DIMENSIONS IN MILLIMETRES

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.
NO PART THEREOF MAY BE REPRODUCED AND USED
WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER

MATERIAL:
SEE COMPONENT

FINISH:
SEE COMPONENT

THIRD ANGLE
PROJECTION

SCALE: **1:1**

DRN: M.H

CKD: M.H

APP'D: P.M

DATE: 11-11-23

DATE: 11-11-23

DATE: 11-11-23

DATE: 11-11-23

SCALE: **1:1**

Amphenol Amphenol Australia Pty.Ltd,
22 Industry Blvd, Carrum Downs, VIC 3201

TITLE:
**AXS5MP2
AXS PANEL MOUNT SERIES
CUSTOMER DRAWING**

CAD FILE: 55011499825110

PART No.
SEE TABLE

DRAWING No.

55011499-825-2

SHEET
2/2