

PRODUCT DATASHEET

FL 200 PCELL P 133W 840 20KLM PS BK

FLOODLIGHT PHOTOCELL 200 | Floodlight with daylight sensor, up to 20000 lm



PERFOR-
MANCE
CLASS

Areas of application

- Replacement for floodlights with halogen lamps
- Outdoor use (IP66)
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, e.g. by accumulation of dust
- Public areas
- Building facades
- Construction areas
- Parking

Product benefits

- Automatically switches on and off according to the amount of available daylight
- Always-on override, activated via special mains switching pattern
- Breather membrane to optimize air exchange, without compromising IP protection
- Highly versatile due to selectable lumen steps (Multi Lumen) on the housing
- Robust cable gland with integrated waterstop function
- Safe and very uniform illumination, due to frosted and tempered glass diffuser
- Bright, robust and durable
- No upper light output ratio (ULOR 0%) when mounted at 0° tilt
- Energy savings of up to 90 % compared to halogen lamp floodlights

Product features

- Daylight sensor, integrated in glass cover
- Switch on below 35 lux, switch off above 95 lux illuminance
- High luminous efficacy: up to 150 lm/W
- Type of protection: IP66
- Pre-installed, flexible 1 m cable (H05RN-F), wrapped 3 x 1.0 mm² single wires
- Reflector-based, symmetric light distribution with 100° x 100° beam angle
- Mounting bracket with 30° angle and wide rotation area
- Integrated voltage driver, suitable for 220 - 240 V AC


TECHNICAL DATA

Electrical data


Nominal wattage	133 W / 117 W
Nominal voltage	220...240 V
Mains frequency	50...60 Hz
Nominal current	590/519 mA
Inrush current	34.6 A
Inrush current time T_{h50}	552 μ s
Max. number of luminaires per miniature circuit breaker B16	4
Max. number of luminaires per miniature circuit breaker C10	4
Max. number of luminaires per miniature circuit breaker C16	7
Power factor λ	> 0.90
Total harmonic distortion	< 20 %
Protection class	I
Surge capability (L-N)	4 kV
Surge capability (L/N-Ground)	6 kV
Operating mode	Integrated LED driver

Photometrical data

Luminous flux	20000 lm / 17500 lm
Luminous efficacy	150 lm/W
Color temperature	4000 K
Light color (designation)	Cool White
Color rendering index Ra	80
Standard deviation of color matching	5 sdc _m
Stroboscope effect metric (SVM)	≤0.9
Photobiological safety group acc. to EN62778	RG1
Photobiological safety group acc. to EN62471	RG1
Beam angle	100 ° x 100 °



FL 200 PCELL P 133W 840 20KLM PS BK




FL 200 PCELL P 133W 840 20KLM PS BK

Adjustable attributes

Nominal wattage	Color temperature	Luminous flux	Luminous efficacy
133 W	4000 K	20000 lm	150 lm/W
117 W	4000 K	17500 lm	150 lm/W

Dimensions & Weight

Length	294.00 mm
Width	58.00 mm
Height	376.00 mm
Product weight	3484.00 g
Cable length	1000 mm



Materials & Colors

Product color	Black
Housing color	Black
RAL Color (most similar)	RAL 9017
Body material	Aluminum
Cover material	Glass
Light emitting surface material	Glass
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

Ambient temperature range	-30...+50 °C
Temperature range at storage	-40...+70 °C
Type of connection	Cable, 3-pole
Type of protection	IP66
Protection class IK (shock resistance)	IK08
Corrosion resistance class acc. to EN 12944	C4
Dimmable	No
Mounting type	Surface
Mounting location	Wall / Pole / Floor
Application environment	Outdoor
Mechanically adjustable	Yes
With light source	Yes
Replaceable light source	No

Lifespan

Lifespan L70/B50 at 25 °C	100000 h ¹⁾
Lifespan L80/B10 at 25 °C	75000 h ¹⁾
Lifespan L80/B50 at 25 °C	70000 h
Lifespan L90/B10 at 25 °C	35000 h

¹⁾ t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

Control gear

Output current	630 mA
ECG - Output ripple current	< 20 %

Sensor

Type of sensor	Light
----------------	-------

Sensor technology	Photocell
Detection threshold of daylight sensor	35...95 lx
Sensor IP rating	IP66

Certificates & Standards

Standards	CE / CB / ENEC / EAC / UKCA / EPD
Luminaire with limited surface temperature, "D sign"	Yes
Ball shot safe	No
EPD	LEDV-00030-V01.01-EN

Additional product data

Added function	MULTI SELECT
----------------	--------------

Accessories Optional

Product image	Product name	EAN
	FL TRAVERSE 1/2 42/60/76MM	4099854680038

Safety advice

– Max. wind load surface 0.085 m²

DOWNLOAD DATA

Documents and certificates		Document name
	User instruction / safety instructions	G11193709_UI_Floodlight_Photocell
	Legal information	Insert_LSI_Floodlight_Sensor_Photocell_G11195969
	Legal information	Informationstext 18 Abs 4 ElektroG
	Legal information	Safety Insert G11205496
	Legal information	Legal Insert G11277401
	Declarations of conformity	FLOODLIGHT GEN4
	Declarations of conformity UKCA	FLOODLIGHT GEN4

Documents and certificates		Document name
	EPD	EPD EN FLOODLIGHT GEN 4 MP PHOTOCELL

Photometric and lighting design files		Document name
	IES file (IES)	FL 200 PCELL P 133W 840 20KLM PS BK
	LDT file (Eulumdat)	FL 200 PCELL P 133W 840 20KLM PS BK
	ULD file (DIALux)	FL 200 PCELL P 133W 840 20KLM PSBK
	ROLF file (RELUX)	FL 200 PCELL P 133W 840 20KLM PSBK
	UGR file (UGR table)	FL 200 PCELL P 133W 840 20KLM PS BK
	Light distribution curve type cone	FL 200 PCELL P 133W 840 20KLM PS BK
	Light distribution curve type polar	FL 200 PCELL P 133W 840 20KLM PS BK

CAD/BIM files		Document name
	BIM Revit 3D	Floodlight G4
	CAD STEP 3D	FL G4 133W


Tender texts		Document name
	Tender documents	FLOODLIGHT PHOTOCELL 200 133W 840 20KLM PS BK-EN

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854307041	Folding box 1	75 mm x 324 mm x 417 mm	3785.00 g	10.13 dm³
4099854307058	Shipping box 2	340 mm x 167 mm x 444 mm	8069.00 g	25.21 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

ADDITIONAL CATALOG INFORMATION

				230 Vac		
	A	B	C			
60W	150	108	8.5	2x M8	0.045 m²	
100W	150	108	10.5	2x M8	0.070 m²	
133W	170	118	10.5	2x M8	0.085 m²	
					C10A	B10A C10A
						
					25	41 41
					6	5 9
					4	4 7

	
FL 100 PCELL P 60W AND 10KLM PS	60 W / 8000 lm
FL 100 PCELL P 100W AND 10KLM PS	100 W / 10000 lm
FL 100 PCELL P 133W AND 20KLM PS	133 W / 20000 lm

References / Links

– For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.