



Connectors > Rectangular Connectors > Standard Rectangular Connectors > DYNAMIC 1100 REC AND TAB HSG



Connector Product Type: **Housing**

Connector System: **Wire-to-Wire**

Number of Positions: **32**

Centerline (Pitch): **2 mm [.079 in]**

Number of Rows: **2**

[All DYNAMIC 1100 REC AND TAB HSG \(50\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	32
Number of Rows	2

Mechanical Attachment

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

Usage Conditions



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Dynamic 1000 Series




Connector Contacts(40)



Connector Hardware(3)



Insertion & Extraction Tools(2)




PCB Headers & Receptacles(169)



Power Contacts(9)



Rectangular Power Connectors(111)



Wire-to-Board Headers & Receptacles (169)

Customers Also Bought



TE Part #2295044-6
RITS CONN. PLUG ASSY 6P YELLOW
TIN



TE Part #CAT-526SDL-SEALSE
Connector Seals: 2.55 mm, Signal
Double Lock



TE Part #4-2295044-3
RITS CONN. PLUG ASSY 3P GREEN
TIN



TE Part #1-1903128-0
DYNAMIC 1100D TAB HSG 40P P/M



TE Part #1473567-4
RITS CONN.HDR ASSY 4ROW 4P



TE Part #CAT-D9934-A75C
DYNAMIC 3500 REC AND TAB HSG



TE Part #2312736-2
HMN-HD4-6-F

Documents

Product Drawings
DYNAMIC 1100D TAB HSG 32P P/M
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-1903128-6_N.2d_dxf.zip



English

Customer View Model

ENG_CVM_CVM_1-1903128-6_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1903128-6_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

English

Agency Approvals

UL

English