

Product data sheet

Specifications



Repacked voltage control relay,
Harmony Control Relays, 5A, 1CO,
overvoltage and undervoltage
detection, 65...260V AC DC

RM17UBE15W



This repacked option saves 2.131 over the standard condition

Main

Range of product	Harmony Control Relays
Relay type	Voltage control relay
Product or component type	Voltage control relay
Product specific application	For single-phase and DC supply
Relay name	RM17UBE
Relay monitored parameters	Overvoltage and undervoltage detection
time delay	Adjustable 0.1...10 s, 0 + 10 % Tt- time delay upon fault
Switching capacity in VA	1250 VA
Measurement range	65...260 V AC/DC
Contacts type and composition	1 C/O

Complementary

Reset time	1500 ms time delay
Maximum switching voltage	250 V AC/DC
Minimum switching current	10 mA at 5 V DC
Maximum switching current	5 A AC/DC
Supply voltage limits	50...270 V AC/DC
Power consumption in VA	0...3 VA AC
Maximum power consumption in W	1 W DC
Control circuit frequency	50...60 Hz +/- 10 %
Immunity to microbreaks	20 ms
Output contacts	1 C/O
Nominal output current	5 A
Hysteresis	5 % fixed of threshold setting
Measurement accuracy	+/- 10 % of the full scale value
Polarity	Non reversible polarity on DC supply
delay at power up	1000 ms DC 500 ms AC
Maximum measuring cycle	150 ms measurement cycle as true rms value
Repeat accuracy	+/- 0.5 % for input and measurement circuit +/- 1 % for time delay

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Measurement error	< 1 % over the whole range with voltage variation 0.2 %/°C with temperature variation
Quality labels	CE
Insulation resistance	> 500 MOhm at 500 V DC conforming to IEC 60255-5 > 500 MOhm at 500 V DC conforming to IEC 60664-1
Operating position	Any position without derating
Local signalling	LED (green) for power ON LED (yellow) for relay ON
Overvoltage category	III conforming to IEC 60664-1
[Ui] rated insulation voltage	250 V conforming to IEC 60664-1 400 V conforming to IEC 60664-1
Connections - terminals	Screw terminals, 1 x 0.5...1 x 4 mm² (AWG 20...AWG 11) solid without cable end Screw terminals, 2 x 0.5...2 x 2.5 mm² (AWG 20...AWG 14) solid without cable end Screw terminals, 1 x 0.2...2 x 2.5 mm² (AWG 24...AWG 12) flexible with cable end Screw terminals, 2 x 0.2...2 x 1.5 mm² (AWG 24...AWG 16) flexible with cable end
Tightening torque	0.6...1 N.m conforming to IEC 60947-1
Housing material	Polycarbonate
Mounting support	35 mm symmetrical DIN rail conforming to IEC 60715
Electrical durability	100000 cycles
Mechanical durability	30000000 cycles
Operating rate	<= 360 operations/hour full load
Utilisation category	AC-12 conforming to IEC 60947-5-1 AC-13 conforming to IEC 60947-5-1 AC-14 conforming to IEC 60947-5-1 AC-15 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1 DC-14 conforming to IEC 60947-5-1
[Un] rated nominal voltage	, self-powered
Safety reliability data	B10d = 470000 MTTFd = 502.2 years
Control type	Without test button
Width	17.5 mm
Product weight	0.08 kg

Environment

Electromagnetic compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments conforming to IEC 61000-6-3 Immunity for industrial environments conforming to NF EN/IEC 61000-6-2
Ambient air temperature for operation	-20...50 °C
Vibration resistance	0.35 mm (f= 5...57.6 Hz) conforming to IEC 60068-2-6 1 gn (f= 57.6...150 Hz) conforming to IEC 60255-21-1
Shock resistance	5 gn conforming to IEC 60068-2-27
Standards	IEC 60255-6
Product certifications	UL GL GOST C-Tick CSA
Ambient air temperature for storage	-40...70 °C

Relative humidity	95 % at 55 °C conforming to IEC 60068-2-30
IP degree of protection	IP20 (terminals) conforming to IEC 60529 IP30 (casing) conforming to IEC 60529
Pollution degree	3 conforming to IEC 60664-1
Directives	73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility
Dielectric test voltage	2 kV, 1 min AC 50 Hz conforming to IEC 60255-5 2 kV, 1 min AC 50 Hz conforming to IEC 60664-1
Non-dissipating shock wave	4 kV conforming to IEC 60255-5 4 kV conforming to IEC 60664-1 4 kV conforming to IEC 61000-4-5

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.800 cm
Package 1 Width	7.800 cm
Package 1 Length	9.700 cm
Package 1 Weight	81.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Lower carbon footprint	2 kg CO2 eq.

Use Better

 Materials and Substances	
SCIP Number	5e3fdf99-611b-4d07-ad17-6eba84ab488b
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

 Lifetime extension	
Repair	No

Image of product / Alternate images

Alternative





