

Specifications



Eaton 132419

Eaton Moeller series xEffect - FAZ-NA, FAZ-RT MCB. Miniature circuit breaker (MCB), 5 A, 1p, characteristic: B UL

General specifications

PRODUCT NAME	Eaton Moeller series xEffect - FAZ-NA, FAZ-RT MCB
CATALOG NUMBER	132419
MODEL CODE	FAZ-B5/1-NA
EAN	4015081293582
PRODUCT LENGTH/DEPTH	105 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	17.7 mm
PRODUCT WEIGHT	0.121 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC 60947-2 UL 489 CE marking IEC/EN 60947-2 CSA (File No. 204453) UL (Category Control Number DIVQ) UL 489, CSA C22.2 No. 5 CSA (Class No. 1432-01) CSA-C22.2 No. 5-09 Specially designed for North America, suitable as BCPD UL (File No. E235139) North America (UL listed, CSA certified) EN45545-2 IEC 61373
GLOBAL CATALOG	132419



Powering Business Worldwide

Product specifications

USED WITH	Miniature circuit breaker FAZ-NA
AMPERAGE RATING	5 A
VOLTAGE RATING	277 V AC / 480 V AC
FEATURES	Additional equipment possible
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

Resources

BROCHURES	eaton-pdd-railrolling-stock-brochure-br011002en-en-us.pdf
CATALOGS	eaton-xeffect-faz-na-rt-mcb-catalog-ca003032en-en-us.pdf
CHARACTERISTIC CURVE	eaton-xeffect-faz-na,-mcb-characteristic-curve-002.jpg eaton-xeffect-faz-na,-mcb-dimensions-002.jpg eaton-xeffect-faz-na,-mcb-characteristic-curve.jpg
DECLARATIONS OF CONFORMITY	eaton-mcb-declaration-of-conformity-eu250394en.pdf
DRAWINGS	eaton-mcb-xeffect-faz-na.-3d-drawing.eps
ECAD MODEL	DA-CE-ETN.FAZ-B5_1-NA
INSTALLATION INSTRUCTIONS	IL019133ZU
MCAD MODEL	faz_na_1p.dwg faz_na_1p.stp eaton-non-selective-universal-mcb-mcad-3d-models-faz-na-rt-1p.stp
WIRING DIAGRAMS	eaton-xpole-mmc4-6-m-mcb-wiring-diagram-002.jpg eaton-mcb-xeffect-faz-na.-wiring-diagram.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	45 mm
POLLUTION DEGREE	2
MOUNTING METHOD	Top-hat rail IEC/EN 60715
DEGREE OF PROTECTION	IP20 UL/CSA Type: - IP20 (IEC) IP40 (when fitted)
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	1.8 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
BREAKING CAPACITY	10 kA (UL489)
TERMINAL PROTECTION	Finger and hand touch safe, DGUV VS3, EN 50274
TERMINALS (TOP AND BOTTOM)	Twin-purpose terminals
TRIPPING CHARACTERISTIC	B
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS	25 mm ²

SECTION (MULTI-WIRED) - MAX	
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
ENCLOSURE WIDTH	105 mm
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT	0 W
DIRECTION OF INCOMING SUPPLY	As required
WIDTH IN NUMBER OF MODULAR SPACINGS	1
VOLTAGE RATING (IEC/EN 60947-2)	254 V
VOLTAGE RATING (UL)	277 V
VOLTAGE RATING AT DC	60 V DC
VOLTAGE TYPE	AC
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Single-pole
FUNCTIONS	Current limiting circuit breaker
LIFESPAN, ELECTRICAL	20000 operations
RELEASE CHARACTERISTIC	B
TYPE	<ul style="list-style-type: none"> • FAZ-NA • Miniature circuit breaker
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a

	0.5% linear reduction of current carrying capacity
APPLICATION	<ul style="list-style-type: none"> • Feeder circuits, branch circuits • Switchgear for export to North America (UL-listed)
MOUNTING WIDTH	17.7 mm
SELECTIVITY CLASS	3
MOUNTING WIDTH PER POLE	17.7 mm
NUMBER OF POLES (PROTECTED)	1
NUMBER OF POLES (TOTAL)	1
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	5 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	240 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	0 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V	0 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	15 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V	15 kA
RATED SWITCHING CAPACITY (IEC/EN 60947-2)	15 kA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
TIGHTENING TORQUE	Max. 2.4 Nm UL: 2.8 Nm (25 lb-in) for AWG 10 - AWG 8 UL: 4 Nm (36 lb-in) for AWG 6 UL: 2.4 Nm (21 lb-in) for AWG 18 - AWG 12
POWER LOSS	1.9 W

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.