

Features

- Steel Toe Cap that provides 200 Joules protection
- Printed leather
- Dual density PU sole that is oil-resistant and anti-static
- 3 pairs of eyelets for easy threading
- Full length EVA foam contoured footbed for superior comfort

RS PRO R102 Lace Up Safety Shoe

RS article number	MPN	Colour
246-1004	R102-03	Black
246-1005	R102-04	Black
246-1006	R102-05	Black
246-1007	R102-06	Black
246-1008	R102-07	Black
246-1009	R102-08	Black
246-1010	R102-09	Black
246-1011	R102-10	Black
246-1012	R102-11	Black
246-1013	R102-12	Black
246-1014	R102-13	Black
246-1015	R102-14	Black



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

## RS PRO R102 Lace Up Safety Shoes offer:

- Steel toe cap that provides 200 joules protection
- Printed leather
- Stainless steel midsole to provide penetration resistance to a minimum of 1100 Newtons
- Dual density polyurethane sole that is oil resistant and antistatic
- Padded polyurethane collar and tongue backed with nylon mesh lining
- Black nylon stitching with excellent abrasion resistance and wicking, breathable sandwich mesh lining
- 3 metal round eyelets for easy fastening
- 5mm EVA die cut insole with breathable Cambrelle layer for extra comfort and cushioning

## General Specifications

Type	Safety Shoes
Gender	Unisex
Colour	Black
Safety Toe	Yes
Safety Toe Type	Steel Toe Cap
Lining Material	Nylon Mesh Lining
Water Resistant	Yes
Resistant To	Oil
Sole Material	Polyurethane

## Size Chart

Shoe Size UK	3	4	5	6	7	8	9	10	11	12	13	14
Shoe Size EU	36	37	38	39	41	42	43	44	46	47	48	49
Shoe Size US	5	6	7	8	9	10	11	12	13	14	15	16

Safety Rating EN ISO 20345:2011	S2 SRC
European Safety Standard	EN ISO 20345:2011
Declaration	EC Declaration of Conformity / UKCA Declaration of Conformity