

PRODUCT CODE		EC-GS12	12" / 300 mm Heavy Duty Metal Working Clamp				
DIMENSIONAL CRITERIA		SPECIFICATION	Supplier Inspections				
1							
2	Handle & Fixed Arm Material	Zinc coated Forged Steel					
3	Fixed Arm Dimensions	195 ± 3mm x 29.6 ± 1mm x 17 mm ± 0.5mm					
4	Flat Dimensions	70 ± 1mm x 37.5 ± 1mm x 9 mm ± 0.5mm					
5							
6							
7	Head Permissible Angle / Ball Type	30° / Half Ball					
8	Throat Depth	140 mm					
9	Slide Bar material & Colour	Zinc coated Forged Steel					
10							
11							
12							
13							
14	Threaded Bar End	22 mm Hex					
15							
16	Ease of Clamping Operation	Smooth and Easy					
17							
18	Clamping Range	0- 300 mm					
19	Applicable Clamping Force	> 750 Kg					
20	Overall Length, Fully Open	542 ± 3mm					
21	Weight	3.000 Kg ± 0.100 Kg					
22							
23							
24	Barcode, label on Slide bar	5012095618454					
25							
26	Packed	5 per box					
27							
28							
29							

