



Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**  
Switch Contact Plating Material: **Gold**  
Case Color: **Black**  
Case Material: **Polyphenylene Sulfide (PPS)**  
Sealed Device: **Yes**

Features

Product Type Features

Leg Style	Gull Wing
DIP & SIP Switch Type	DIP
Sealed Device	Yes
Actuator Style	Recessed Rocker

Configuration Features

Number of Positions	6
Number of Switches	6
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	.1 A
Operating Voltage	50 VDC

Body Features

Sealing Method	Sealing Tape
Case Color	Black
Case Material	Polyphenylene Sulfide (PPS)

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold



Switch Contact Plating Material	Gold
Contact Base Material	Copper Alloy

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	Yes
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Product Length	8.74 mm[.344 in]
Product Height	2.21 mm[.087 in]

Usage Conditions

Operating Temperature Range	-30 – 85 °C
-----------------------------	-------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
Packaging Quantity	50

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as




EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 <p>TE Part # 1-1571983-1 GDH08STR04=DIP SWITCH</p>	 <p>TE Part # 1571983-4 GDH04S04=DIP SWITCH</p>	 <p>TE Part # 1977830-1 DIP SWITCH GDH02SA04</p>	 <p>TE Part # 1-1571983-7 GDH06STR0N04</p>
 <p>TE Part # 1977830-4 DIP SWITCH GDH08SA04</p>	 <p>TE Part # 1571983-5 GDH04STR04=DIP SWITCH</p>		

Also in the Series | Alcoswitch DIP GDH



DIP & SIP Switches(160)

Also in the Series | Alcoswitch DIP



DIP & SIP Switches(160)




Rotary Switches(16)


Customers Also Bought




TE Part #2213748-1  
COVER,LIGHT CONTROLLER,76MM DIA,MEDIUM




TE Part #215605-4  
96P.IEC-C MALE CONN



TE Part #1623750-6  
ER58 15K 5% AMMO




TE Part #284512-6  
6 POS TERMI-BLOK HDR 900 POLAR



TE Part #5-104655-5  
40 50/50 HDR DRST SFMNT TIN



TE Part #8-1622796-7  
YR1 0.1% 18K2




TE Part #1-2176363-5  
RQ 0402 604R 0.1% 10PPM 5K RL



TE Part #5787973-1  
36 .8MM CHAMP RCPT ASSY



TE Part #5747252-4  
37 MSFL PLUG RA 318 (IN,FM)



TE Part #2176635-6  
3627 322515 10UH 10%

Documents

CAD Files

3D PDF

English

Customer View Model

ENG\_CVM\_1571983-8\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_1571983-8\_B.3d\_igs.zip



English

Customer View Model

[ENG\\_CVM\\_1571983-8\\_B.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1571983-8\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1571983-8\\_C.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1571983-8\\_C.2d\\_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English