




Technical data

7005UADG/GNP42

High precision angular contact ball bearings

VISUAL (S)



7005UADG/GNP42

High precision angular contact ball bearings

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	25 mm
D - External diameter	47 mm
B - Bearing/Inner ring width	12 mm
d1 - External diameter inner ring	32,6 mm
d2 - External diameter inner ring	30,9 mm
D1 - Inner diameter outer ring	39,4 mm
D2 - Inner diameter outer ring	42,8 mm
a - Charge load application point	14,5 mm
- Contact angle	25 °
rs - Min fillet radius	0,6 mm
r1s - Min fillet radius	0,3 mm
Precision class	P42
Mass	0,079 kg

PRODUCT PERFORMANCE

C - Dynamic load	13000000 mN
C0 - Static load	7650000 mN
f0 - Coefficient	14.9
N lim - Oil lubrication limit speed	273599,999 °/s
N lim - Grease lubrication limit speed	169200 °/s
Preload level	GN
Preload value	118000 mN
Axial rigidity	89.7 N/μm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

7005UADG/GNP42

High precision angular contact ball bearings

PRODUCT PERFORMANCE

Radial rigidity	188 N/μm
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	29,5 mm
Da max - Max shoulder diameter OR	42,5 mm
Db max - Max OR shoulder diameter	44,5 mm
r1a - Max fillet radius	0,3 mm
ra max - Max shaft & housing fillet radius	0,6 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

7005UADG/GNP42

High precision angular contact ball bearings

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

Series			e	Single or DT bearing arrangement				DB or DF arrangement				
				Fa / Fr ≤ e		Fa / Fr > e		Fa / Fr ≤ e		Fa / Fr > e		
				X	Y	X	Y	X	Y	X	Y	
70 (NTN & SNR) 72 (NTN & SNR) 78 (NTN) 79 (NTN) 719 (SNR)	15°	0.178	0.38	1	0	0.44	1.47	1	1.65	0.72	2.39	
		0.357	0.4				1.4		1.57		2.28	
		0.714	0.43				1.3		1.46		2.11	
		1.07	0.46				1.23		1.38		2	
		1.43	0.47				1.19		1.34		1.93	
		2.14	0.5				1.12		1.26		1.82	
		3.57	0.55				1.02		1.14		1.66	
		5.35	0.56						1.12		1.63	
		7.14	0.56				1		1.12		1.63	
	25°		0.68				0.41	0.87		0.92	0.67	1.41
	30°		0.8				0.39	0.76		0.78	0.63	1.24

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

Series		Single or DT bearing arrangement		DB or DF arrangement		
		X ₀	Y ₀	X ₀	Y ₀	
70 (NTN & SNR)	15°	0.5	0.46	1	0.92	
72 (NTN & SNR)			25°		0.38	0.76
78 (NTN)	30°				0.33	0.66
79 (NTN)						
719 (SNR)						

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15