

## Features

- Nylon 6/6
- High Quality
- 100x2.5 = x361  
natural, x50 red,  
yellow, blue
- 200x4.8 = 425 nat.
- 280x4.8 = 65 nat
- Easy to use
- Available in a range of  
colours

## RS PRO Cable Ties Value Tub

RS Stock No.: 0267993



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*RS PRO Nylon Non-Releasable Cable Ties. Their primary purpose is to aid clean installations by holding cables together or in a specific location. They however have various other uses such as hanging or storing parts ready to paint. RS PRO Nylon Non-Releasable Cable Ties are made from nylon, easy to use and are an essential item for any toolbox.*

## General Specifications

Type	Non-releasable
Colour	Black, Natural, Red, Yellow and Blue
Material	Nylon 6/6
Application	Bundling wire together, Suitable for use in electrical and electronic servicing, maintenance, mechanical and automotive applications.
Resistant To	Ultraviolet Resistance
UV Resistant	No
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	+85°C
Fire Behaviour	Flame Retardant
Quantity	850

## Mechanical Specifications

Size	100mm x 2.5mm, 200mm x 4.8mm and 280mm x 4.8mm
Tensile Strength	See below chart


## Approvals

Standards Met

UL94V-2

## Similar Products

### Dimensions



RS Article	Colour	Length (mm)	Width (mm)	Quantity	Min. Tensile Strength (Kg)	Max Bundle Dia. (mm)
178-462	Natural	100	2.5	100	8	22
233-499	Black	100	2.5	100	8	22
492-0447	Natural	100	2.5	1000	8	22
233-455	Black	100	2.5	1000	8	22
178-478	Natural	150	3.6	100	18	36
233-465	Black	150	3.6	100	18	36
492-0453	Natural	150	3.6	1000	18	36
233-500	Black	150	3.6	1000	18	36
178-484	Natural	190	4.8	100	22	49
233-461	Black	190	4.8	100	22	49
492-0469	Natural	190	4.8	1000	22	49
233-506	Black	190	4.8	1000	22	49

RS Article	Colour	Length (mm)	Width (mm)	Quantity	Min. Tensile Strength (Kg)	Max Bundle Dia. (mm)
489-2140	Natural	203	4.6	100	22	52
233-471	Black	203	4.6	100	22	52
178-490	Natural	292	3.6	100	18	82
233-477	Black	292	3.6	100	18	82
489-2156	Natural	300	4.8	100	22	83
233-487	Black	300	4.8	100	22	83
178-507	Natural	368	4.8	100	22	105
233-483	Black	368	4.8	100	22	105
233-493	Black	380	7.6	100	55	105

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories