

## FEATURES

- **0.4 A Output Current:** Provides sufficient power for small electronic devices
- **1.5 m Cable Length:** Offers flexibility in device placement
- **79% Efficiency:** Ensures energy savings and reduced heat generation
- **Regulated Output:** Delivers stable voltage for sensitive electronics
- **Wide Input Voltage Range (90-264 V AC):** Compatible with various power sources
- **Compact Dimensions (40 x 37.5 x 21.5 mm):** Saves space and is easy to install
- **EU Plug Type:** Suitable for use in European regions
- **Compliance with BS EN 62368-1, IEC 62368-1:** Meets safety and performance standards

## RS PRO 24V AC/DC Adaptor, 12W EU Plug

RS Stock No: 625-743



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

This RS PRO AC/DC adaptor is designed to convert AC input to a stable 24V DC output, making it ideal for powering a variety of electronic devices. With a compact design and EU plug, it offers convenience and reliability for both industrial and domestic applications.

### General Specifications

Cable Length	1.5 m
Efficiency	79 %
Energy Efficiency Level	VI
Input Connector Type	EU Plug
Number of Outputs	1
Output Connector Type	2.1 x 5.5 x 12 mm Jack
Plug Type	EU
Product Type	AC/DC Adaptor
Regulated/Unregulated	Regulated
Sub Type	External AC/DC EU Plugtop Adaptor Power Supply

### Electrical Specifications

Adapter Current	0.4 A
Maximum Input Voltage	264 V ac
Minimum Input Voltage	90 V ac
Output Voltage	24 V dc
Power	12 W

### Mechanical Specifications

Depth	21.5 mm
Length	40 mm
Width	37.5 mm

### Operation Environment Specifications

Maximum Operating Temperature	60 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals

BS EN 62368-1, IEC 62368-1, REACH, RoHS, UKCA

