





LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E6	REV PER ECR-12-013669	02AUG2012	AY	SZ




- 1 MATERIAL:
HOUSING - GLASS FILLED POLYESTER, COLOR BLACK
CONTACT - PHOSPHOR BRONZE
- 2 FINISH:
(SEE TABLE FOR GOLD PLATING) IN CONTACT AREA.
.000100 MIN MATTE TIN ON SOLDER POSTS. ALL OVER
.000050 MIN THK. NICKEL
- 3 AMP LOGO, TE PART NUMBER, DATE CODE AND CSA LOGO INK STAMPED WHITE (HOT STAMPED OR LAZER PRINTED) IN THE APPROXIMATE AREA SHOWN, EITHER SIDE PERMISSABLE WHEN HOUSING SIZE PERMITS
4. RECOMMENDED PCB FINISHED HOLE $\varnothing .040 \pm .003$
- 5 .000015 MIN
- 6 .000030 MIN
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JAWF/GRZYBOWSKI	30OCT2009	 TE Connectivity	
DIMENSIONS: INCHES		CHK E.HOWARD	-		
		APVD M.PERCHEK	30OCT2009	NAME CONNECTOR ASSEMBLY STANDARD EDGE II, .100 CENTERLINE	
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
0 PLC ±		114-13018			
1 PLC ±.005		WEIGHT		RESTRICTED TO	
2 PLC ±		CUSTOMER DRAWING			
3 PLC ±		SCALE 4:1		SHEET 1 OF 4	
4 PLC ±		REV E7			
ANGLES #2					
FINISH					


D




C



B



A



SECTION A-A

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
AWF/GRZYBOWSKI

CHK
E.HOWARD

APVD
M.PERCHEK

30OCT2009

DIMENSIONS:

INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm .005$

1 PLC $\pm .005$

2 PLC $\pm .005$

3 PLC $\pm .005$

4 PLC $\pm .005$

ANGLES $\pm .005$

FINISH $\pm .005$

MATERIAL

-

PRODUCT SPEC

108-9039

APPLICATION SPEC

114-13018

WEIGHT

-

CUSTOMER DRAWING

NAME

CONNECTOR ASSEMBLY
STANDARD EDGE II,
.100 CENTERLINE

SIZE

CAGE CODE

DRAWING NO

A100779

RESTRICTED TO

-

SCALE

4:1

SHEET

2

OF

4

REV

E7

TE Connectivity

LOC	DIST	REVISIONS						
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		-		SEE SHEET 1	-	-	-	

OBSOLETE	8-5530843-2
OBSOLETE	8-5530843-1
OBSOLETE	4-5530843-1
OBSOLETE	1-5530843-9
OBSOLETE	1-5530843-2
	PART NUMBER

E6

			0.686	-	.500	.700	-	-	5	6	8-5530843-6
			1.286	.187	1.100	1.300	1.350	1.460	11	12	8-5530843-5
19,20,21,22,23,24,27,28,31,32,35,36,39 40,43,44,45,46,47,48,51,52,55,56,59,60	-		3.186	.125	3.000	3.200	3.250	3.360	30	31	8-5530843-4
	3,4,5,6,19,20,21,22		1.286	.125	1.100	1.300	1.350	1.460	11	12	8-5530843-3
	-		.386	.125	.200	.400	.450	.560	2	3	7-5530843-7
	-		.686	.187	.500	.700	.750	.860	5	6	7-5530843-6
	-		.686	.125	.500	.700	.750	.860	5	6	7-5530843-5
	-		3.186	.125	3.000	3.200	3.250	3.360	30	31	7-5530843-0
	-		3.186	.125	3.000	3.200	3.250	3.360	30	31	6-5530843-5
OBSOLETE	-		6.086	.125	5.900	6.100	6.150	6.260	59	60	5-5530843-5
	-		2.086	.125	1.900	2.100	2.150	2.260	19	20	5-5530843-4
	-		1.786	.125	1.600	1.800	1.850	1.960	16	17	5-5530843-3
	-		1.086	.125	.900	1.100	1.150	1.260	9	10	5-5530843-0
	-		1.886	.125	1.700	1.900	1.950	2.060	17	18	2-5530843-7
	-		3.586	.125	3.400	3.600	3.650	3.760	34	35	2-5530843-3
	-		5.086	.187	4.900	5.100	5.150	5.260	49	50	2-5530843-2
	-		4.086	.187	3.900	4.100	4.150	4.260	39	40	2-5530843-0
	-		3.086	.187	2.900	3.100	3.150	3.260	29	30	1-5530843-8
	-		2.586	.187	2.400	2.600	2.650	2.760	24	25	1-5530843-6
	-		4.386	.125	4.200	4.400	4.450	4.560	42	43	1-5530843-0
	-		3.686	.125	3.500	3.700	3.750	3.860	35	36	5530843-8
	-		3.086	.125	2.900	3.100	3.150	3.260	29	30	5530843-7
	-		2.886	.125	2.700	2.900	2.950	3.060	27	28	5530843-6
	-		2.586	.125	2.400	2.600	2.650	2.760	24	25	5530843-5
	-		2.286	.125	2.100	2.300	2.350	2.460	21	22	5530843-4
	-		1.886	.125	1.700	1.900	1.950	2.060	17	18	5530843-3
	-		1.586	.125	1.400	1.600	1.650	1.760	14	15	5530843-2
	-		1.286	.125	1.100	1.300	1.350	1.460	11	12	5530843-1
OMITTED PIN	BOARD RETENTION FEATURE LOCATION (SEE DETAIL Y)	FINISH	Z	J	D	C	B	A	X	NO. OF DUAL POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
AWF/GRZYBOWSKI

CHK
E.HOWARD

APVD
M.PERCHEK

30OCT2009

DIMENSIONS:
INCHES

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
#2

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

MATERIAL

-

PRODUCT SPEC

108-9039

APPLICATION SPEC

114-13018

WEIGHT

-

CUSTOMER DRAWING

NAME

CONNECTOR ASSEMBLY
STANDARD EDGE 11,
.100 CENTERLINE

SIZE

A1

CAGE CODE

00779

DRAWING NO

5530843

RESTRICTED TO

-

SCALE

4:1

SHEET

3

OF



4

REV

E7

TE Connectivity

LOC		DIST		REVISIONS			
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AWF/GRZYBOWSKI	30OCT2009	 TE Connectivity	
DIMENSIONS: INCHES		CHK E.HOWARD	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.PERCHEK	30OCT2009	NAME CONNECTOR ASSEMBLY STANDARD EDGE II, .100 CENTERLINE	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ±.005 ± ± ± #2 -	PRODUCT SPEC 108-9039 APPLICATION SPEC 114-13018 WEIGHT -	SIZE A1	CAGE CODE 00779
MATERIAL -		CUSTOMER DRAWING		SCALE 4:1	SHEET 4
				OF 4	REV E7