

Article No. : 1FL2310-6AC01-1HB0



Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Basic motor data	
Motor type	Permanent-magnet synchronous motor
Motor type	High Inertia
Static torque	35.20 Nm
Static current	13.20 A
Maximum torque	90.00 Nm
Maximum current	35.6 A
Maximum speed	2,100 rpm
Rotor moment of inertia	134.2920 kgcm²
Weight	31.9 kg

Rated data	
SINAMICS S200, 3 AC 380 ... 480 V	
Rated speed	2,000 rpm
Rated torque	33.40 Nm
Rated current	13.2 A
Rated power	7.00 kW

Encoder system	
Encoder system	Absolute encoder singleturn 17 bit

Motor connection	
Connection type	Metal angular connector

Mechanical data	
Design acc. to Code I	IM B5 (IM V1, IM V3)
Vibration severity grade	Grade A
Shaft height	90
Flange size (AB)	180 mm
Centering ring (N)	114.3 mm
Hole circle (M)	200 mm
Screw-on hole (S)	13.5 mm
Overall length (LB)	293.5 mm
Diameter of shaft (D)	35 mm
Length of shaft (E)	80 mm
Length of flange diagonal (P)	228 mm
Shaft end	Shaft with parallel key (half-key balancing)
Color of the housing	Anthracite RAL 7016

