
Product datasheet

Specifications



Multi9 - comb busbar - 1L - 18 mm pitch - 12 modules - 115A

M9XUP112

EAN Code: 3606481192806

Main

Range	Multi9
Product or component type	Comb busbar
mounting mode	Horizontal
Accessory / separate part category	Connection accessory
Lines description	1L
Length in 18 mm modules	12
Standards	UL 489 UL 508 CSA C22.2 No 5 CSA C22.2 No 14-13 EN/IEC 61439-1
Product certifications	CULus

Complementary

Number of ways	12 ways 1 L
Distribution type	L
Poles configuration for 1 way	1 x 1P
Connection pitch	18 mm
Connector type	Tooth
Distance between way	18 mm
Insulation	Insulated
Device presentation	Uncuttable
[Ie] rated operational current	115 A at 40 °C
[Ue] rated operational voltage	480 V AC 50/60 Hz Ph/Ph 277 V AC 50/60 Hz Ph/N
[Ui] rated insulation voltage	1000 V AC 50/60 Hz conforming to UL 508
Mounting location	Top on tunnel type terminals
9 mm pitches	24
Width	216 mm
Colour	Light grey (RAL 7035)
Range compatibility	Multi9 C60BP

Environment

Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Pollution degree	3
IP degree of protection	IP20 with end-pieces and tooth covers

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	8.500 cm
Package 1 Length	24.000 cm
Package 1 Weight	124.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	50
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.543 kg

Logistical informations

Country of origin	MK

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**2 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**0.6 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**0 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**0 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**0.7 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**0.3 kg CO2 eq.**
Environmental Disclosure	**Product Environmental Profile**

Use Better

Materials and Substances

Packaging made with recycled cardboard	**No**
Packaging without single use plastic	**No**
SCIP Number	**12618b2a-bc0e-4c2d-bb7b-9185c26e01fe**
EU RoHS Directive	**Compliant**
REACh Regulation	**Reference contains Substances of Very High Concern above the threshold**
Halogen-free status	**Halogen free plastic parts product**
PVC free	**Yes**

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**67**
End of life manual availability	**No need of specific recycling operations**
Take-back	**No**
WEEE Label	**The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**