


Parker Product Datasheet



Parker Legris recoil tubing has a lasting memory after multiple uses, offering an alternative to reels for excellent ergonomics and space saving.

The pre-assembled tubes are equipped with a protection spring, preventing damage to the ends.

PART NUMBER: 1472P08 07 13
COLOR: ORANGE
CONNECTION TYPE: With Threaded Connector
LENGTH: 6 m
TUBE MATERIAL: PA (60 shoreD)
TUBE I.D. (MM): 6
TUBE O.D. (MM): 8
CONNECTION 1 THREAD SIZE (METRIC): BSPT R1/4

PRODUCT OVERVIEW

Parker Legris recoil tubing has a lasting memory after multiple uses, offering an alternative to reels for excellent ergonomics and space saving.

The pre-assembled tubes are equipped with a protection spring, preventing damage to the ends.

Features/Benefits:

- Excellent Mechanical Properties

- Low pressure drop
- Good chemical compatibility

- Self-retracting
- Identical technical performance to PA tubing
- Silicone-free

- Comprehensive Range

- Ready-to-use
- Various colours for circuit identification
- Available with pre-assembled connectors

Markets:

- Machine Tools
- Primary Metal Refining and Processing
- Miscellaneous Manufacturing
- Vehicle Assembly Facilities
- Transportation

Applications:

- Compressed Air and Lubricants Conveying
- Maintenance Workshop
- Industrial Cleaning
- Car Washing
- Power Hand Tools

Technologies:

- Polyamide Tubing
- PA Tubing
- Recoil Tubing
- Industrial Tubing

Technical Characteristics:

- Fluids: Compressed air, lubricants, Other fluids: please consult us
- Materials: Polyamide (68 Shore D)
- Pressure: Vacuum to 20 bar
- Temperature: -20°C to +80°C

Regulations:

- DI: 97/23/EC (PED)
- RG: 1907/2006 (REACH)
- DI: 2002/95/EC (RoHS), 2011/65/EC

Product Types:

- Polyamide (PA) Recoil Tubing

TECH SPECIFICATIONS

MAXIMUM OPERATING TEMPERATURE	80 °C
DIVISION	Low Pressure Connectors Europe Division
MAXIMUM OPERATING PRESSURE	20 barg
MINIMUM OPERATING TEMPERATURE	-20 °C
SPECIFICATIONS MET	REACH 1907/2006/CE
SPECIFICATIONS MET	RoHS 2002/95/EC, 2011/65/EC
SPECIFICATIONS MET	PED 97/23/EC
MEDIA	Air (Compressed Air)
MEDIA	Other Fluids (Please consult us.)
MEDIA	Lubricants
APPLICATION	MRO
APPLICATION	Lubrication
APPLICATION	Robotics
APPLICATION	Pneumatic Tools
APPLICATION	Industrial Cleaning
APPLICATION	Car Washing
APPLICATION	Transportation

VACUUM PRESSURE RATING	755 mm-Hg
WEIGHT	0.329 kg/package
NUMBER OF TUBES	1