

## Han 16 A-asg2-LB-K-16



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 20 016 0296                                                                |
| Specification      | Han 16 A-asg2-LB-K-16                                                         |
| HARTING eCatalogue | <a href="https://harting.com/09200160296">https://harting.com/09200160296</a> |

### Identification

|                             |                           |
|-----------------------------|---------------------------|
| Category                    | Hoods / Housings          |
| Series of hoods/housings    | Han A <sup>®</sup>        |
| Type of hood/housing        | Surface mounted housing   |
| Description of hood/housing | With thermo-plastic cover |
| Type                        | Low construction          |

### Version

|                            |                                                     |
|----------------------------|-----------------------------------------------------|
| Size                       | 16 A                                                |
| Version                    | Side entry                                          |
| Number of cable entries    | 2                                                   |
| Cable entry                | 2x Pg 16                                            |
| Locking type               | Single locking lever                                |
| Han-Easy Lock <sup>®</sup> | Yes                                                 |
| Field of application       | Standard Hoods/housings for industrial applications |

### Technical characteristics

|                                        |                                                |
|----------------------------------------|------------------------------------------------|
| Limiting temperature                   | -40 ... +125 °C                                |
| Note on the limiting temperature       | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65                                           |
| Type rating acc. to UL 50 / UL 50E     | 4<br>4X<br>12                                  |



Pushing Performance  
Since 1945

## Material properties

|                                                            |                                                                   |
|------------------------------------------------------------|-------------------------------------------------------------------|
| Material (hood/housing)                                    | Aluminium die-cast                                                |
| Surface (hood/housing)                                     | Powder-coated                                                     |
| Colour (hood/housing)                                      | RAL 7037 (dust grey)                                              |
| Material (locking)                                         | Polycarbonate (PC)<br>Stainless steel                             |
| Colour (locking)                                           | RAL 7037 (dust grey)                                              |
| Material flammability class acc. to UL 94 (locking levers) | V-0                                                               |
| RoHS                                                       | compliant with exemption                                          |
| RoHS exemptions                                            | 6(c): Copper alloy containing up to 4 % lead by weight            |
| ELV status                                                 | compliant with exemption                                          |
| China RoHS                                                 | 50                                                                |
| REACH Annex XVII substances                                | Not contained                                                     |
| REACH ANNEX XIV substances                                 | Not contained                                                     |
| REACH SVHC substances                                      | Yes                                                               |
| REACH SVHC substances                                      | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate<br>Lead |
| ECHA SCIP number                                           | 2d63e3a4-7abb-4e67-bb13-55bff2df44a0                              |
| California Proposition 65 substances                       | Yes                                                               |
| California Proposition 65 substances                       | Lead<br>Nickel                                                    |
| Fire protection on railway vehicles                        | EN 45545-2 (2020-08)                                              |
| Requirement set with Hazard Levels                         | R22 (HL 1-3)<br>R23 (HL 1-3)                                      |

## Specifications and approvals

|           |                                                            |
|-----------|------------------------------------------------------------|
| UL / CSA  | UL 1977 ECBT2.E235076<br>CSA-C22.2 No. 182.3 ECBT8.E235076 |
| Approvals | CE<br>DNV GL                                               |

## Commercial data

|                                |          |
|--------------------------------|----------|
| Packaging size                 | 1        |
| Net weight                     | 220 g    |
| Country of origin              | Germany  |
| European customs tariff number | 85389099 |



**Pushing Performance**  
Since 1945

## Commercial data

|             |                                          |
|-------------|------------------------------------------|
| GTIN        | 5713140039650                            |
| eCl@ss      | 27440202 Shell for industrial connectors |
| ETIM        | EC000437                                 |
| UNSPSC 24.0 | 39121466                                 |