

Product data sheet

Specifications



Repacked buzzer, New Unica, buzzer, 2 modules, white

NU378518W



This repacked option saves 0.62 over the standard condition

Main

Range	New Unica
Device application	Signalling
Product or component type	Buzzer
Device presentation	Mechanism
[Ue] rated operational voltage	230 V AC 50/60 Hz
Number of modules	2 modules
fixing mode	Clip-in
Colour tint	White (RAL 9003)

Complementary

Current consumption	40 mA
Type of setting	Volume can be adjusted using a screw
Device mounting	Flush
Operating time	<= 30 ms
Connections - terminals	Screw terminals
Acoustic level	Between 76 and 80 dB
Cable cross section	0.75...1.5 mm² flexible cable 0.75...1.5 mm² rigid cable
Material	Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing
Standards	EN 62080 CE
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Embedding depth	31 mm
Depth	50 mm
Width	45 mm
Height	45 mm
Product weight	0.091 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

resistance to chemical agents	Resistant to alcohol (70 %)
	Resistant to alcohol (96 %)
	Resistant to A-Lactic Acid
	Resistant to diluted quaternary ammonium
	Resistant to diluted bleach
	Resistant to diluted ammonia
	Resistant to soapy water
	Resistant to crystal cleaner
	Resistant to hydrogen peroxide 10 volumes
	Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	4.500 cm
Package 1 Length	5.000 cm
Package 1 Weight	52.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.228 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.6 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

6edbd8bf-8086-4f8e-a012-80f9e4a1db80

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins