

## Screwdriver - SF-BIT-HEX 6-50 - 1212650

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw bit, hexagon, E6.3-1/4" drive, size: Hex 6 x 50 mm, hardened, suitable for holder according to DIN 3126-F6.3/ISO 1173

### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 046356 662789
GTIN	4046356662789
Weight per Piece (excluding packing)	13.280 g
Custom tariff number	82079030
Country of origin	Czech Republic

### Technical data

#### General

Color	silver
-------	--------

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Drawings

Pictogram



### Classifications

#### eCl@ss

eCl@ss 10.0.1	21044290
eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402

# Screwdriver - SF-BIT-HEX 6-50 - 1212650

## Classifications

### eCl@ss

eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21044201
eCl@ss 8.0	21044201
eCl@ss 9.0	21044290

### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC002114
ETIM 5.0	EC002114
ETIM 6.0	EC002114

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

## Approvals

### Approvals

---

Approvals
-----------

EAC
-----

Ex Approvals
--------------

### Approval details

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------

## Accessories

### Accessories

### Screwdriver tools

## Screwdriver - SF-BIT-HEX 6-50 - 1212650

### Accessories

Screwdriver - SF-M BH - 1212070



Bit screwdriver, with 1/4" quick-action chuck, handle length 119 mm, 2-component handle, with non-slip grip, suitable for bits according to DIN 3126-C 6.3 and E 6.3/ISO 1173, magnetic

---

Phoenix Contact 2019 © - all rights reserved  
<http://www.phoenixcontact.com>